

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER ECO-19-011232	07AUG2019	RS	MZ



- THIS PART WILL ACCEPT FOUR (4) MULTIMATE PIN CONTACTS.
- HOUSING AND PRESSURE PLATE: NYLON, BLACK.  
PERIPHERAL SEAL: ELASTOMER, BLACK.  
WIRE ENTRY SEAL: ELASTOMER, RED-IRON OXIDE.

796096-2  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.DORWART	24 SEP 98	TE Connectivity RECEPTACLE ASSEMBLY, 11-4, STANDARD SEX, SERIES I, SEALED, CIRCULAR PLASTIC CONNECTOR	RESTRICTED TO -										
DIMENSIONS: mm [INCHES]		CHK R.WALTER	24 SEP 98												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.WALTER	24 SEP 98												
<table border="0"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± 0.13 [0.005]</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -			1 PLC	± -	2 PLC	± 0.13 [0.005]	3 PLC	± -	4 PLC	± -	ANGLES	± -
0 PLC	± -														
1 PLC	± -														
2 PLC	± 0.13 [0.005]														
3 PLC	± -														
4 PLC	± -														
ANGLES	± -														
MATERIAL	FINISH	APPLICATION SPEC	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO								
				A3	00779	C=796096									
CUSTOMER DRAWING				SCALE	SHEET	REV									
				2:1	1 OF 1	A									