




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECN-23-230183	07SEP2023	DW	JH



- NOTE : UNLESS OTHERWISE SPECIFIED
1. FABRICATE TO MEET IPC – 6012, CLASS 2.
INSPECT TO MEET IPC – A – 600, CLASS 2.
 2. MATERIALS
 - 2.1. ANTENNA MATERIAL : Tin PLATE, THICKNESS : 0.2t
 - 2.2. EVB MATERIAL : FR4 PCB, OVERALL THICKNESS 1.00mm
 - 2.3. SMA(FEMALE) PANEL TYPE CONN. : 50 OHMS(IMPEDANCE)
 - 2.4. MEASURED WITH MATCHING CIRCUIT CONDITIONS.
 3. GENERAL TOLERANCES : ± 0.20
 4. PACKAGING : SEE SHEET2
 5. CONSULT TE CONNECTIVITY DATA SHEET DS2108964.
 6. SILKSCREEN : WITHE EPOXY INK.
 - A: TE LOGO, TE P/N
 - B: WORD REV., FOLLOWED BY THE LASTEST REVISION LETTER. AS SHOWN.
 - C: 4 DIGITS DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2 DIGITS FOR THE YEAR CODE.
 - OTHERS: SPECIFIC TE INTERNAL USE ONLY.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	08AUG2022	TE Connectivity			
		CHK H.SHIN	08AUG2022				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD CY.PARK	08AUG2022	NAME 2108964-1 ANTENNA WITH EVB ASSY			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL —		FINISH —	CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-8-2108964
				SCALE 1:1	SHEET 1 of 2	REV A1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




8-2108964-1



BUFFER SPONGE




INDIVIDUAL BOX




1 PC/1 Individual Box

Induividual box Label



100 PCS Individual Box / 1 Carton Box



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DW.PARK	08AUG2022	TE Connectivity		
		CHK H.SHIN	08AUG2022			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD CY.PARK	08AUG2022	NAME 2108964-1 ANTENNA WITH EVB ASSY		
		PRODUCT SPEC	—	—		
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APPLICATION SPEC	—	SIZE	CAGE CODE	DRAWING NO
		WEIGHT	—	A3	00779	C-8-2108964
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	SHEET	REV
—	—			1:1	2 OF 2	A1