




LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
GP		00								L		0B50LETE -4 PER 051D-0014-00		040CT00		JR	



- △ HOUSING-MATERIAL : LIQUID-CRYSTAL-POLYMER.
- △ CONTACT-MATERIAL : PHOS. BRONZE.
- △ LATCH-MATERIAL : BRASS, NICKEL PLATE.
- △ CONTACT-PLATE 0.00127 [.000050] MIN NICKEL ALL OVER.
- △ CONTACT-PLATE 0.00076[.000030] MIN. GOLD AT CONTACT PTS.
- △ CONTACT SOLDER TAILS-PLATE 0.00508[.000200] MIN TIN/LEAD.
7. IN ADDITION TO THOSE RECOMMENDED "SIMM" P.C. BOARD DIMENSIONS AND TOLERANCES SHOWN, ALL JEDEC SPECIFICATIONS APPLY AS SHOWN ON M0-116, ISSUE A.
8. RECOMMENDED MATING S.I.M.M. TAB METALLURGY:
BASE METAL-COPPER. PLATING TO BE 0.00076[.000030] MIN GOLD OVER 0.00127[.000050] MIN NICKEL.



OBSOLETE	118.11 [4.650]	111.35 [4.384]	60.96 [2.400]	49.53 [1.950]	125.73 [4.950]	105.41 [4.150]	80	822033-5
OBSOLETE	107.95 [4.250]	101.19 [3.984]	55.88 [2.200]	44.45 [1.750]	115.57 [4.550]	95.25 [3.750]	72	822033-4
OBSOLETE	102.87 [4.050]	96.11 [3.784]	53.34 [2.100]	41.91 [1.650]	110.49 [4.350]	90.17 [3.550]	68	822033-3
OBSOLETE	97.79 [3.850]	91.03 [3.584]	50.80 [2.000]	39.37 [1.550]	105.41 [4.150]	85.09 [3.350]	64	822033-2
	67.31 [2.650]	60.55 [2.384]	35.56 [1.400]	24.13 [1.950]	74.93 [2.950]	54.61 [2.150]	40	822033-1
F	E	D	C	B	A	NO OF POSN		PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON :
2 PLC DEC ± -
3 PLC DEC ± 0.13[.005]
ANGLES ± -

DR 3-21-91
K.SALMON
CHK 3-25-91
R.MILLER
APPD 3-26-91
J.LAMBERT
APPD 3-26-91
E.MCCARTHY
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -



AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
CONN, MICRO-EDGE, .05 X .4,
VERT, GOLD PL, W/METAL LATCH

SIZE **D** CAGE CODE 00779 DRAWING NO C-822033
SCALE 4:1 SHEET 1 OF 2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

LOC		DIST	REVISIONS				DATE		APPD
GP	00	P	F	ZONE	LTR	DESCRIPTION			
				L		SEE SHEET 1			



SECTION X-X
SCALE 10:1
(BOARDS SHOWN FOR REF ONLY)

PART NO					
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES]			AMP Incorporated Harrisburg, PA 17105-3608		
TOLERANCES ON:			NAME		
2 PLC DEC ± -			CONN, MICRO-EDGE, .05 X .4,		
3 PLC DEC ±0.13[.005]			VERT, GOLD PL, W/METAL LATCH		
ANGLES ± -			SIZE		
MATERIAL			D 00779 C-822033		
SEE SHEET 1			SCALE 4:1		
FINISH			SHEET 20F2		
SEE SHEET 1			CUSTOMER DRAWING		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.