

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	PART OBSOLESCENCE	25JUN2024	RS	VG

POS.	PART-NO.	
-	-	-
2	826654	-2
3		-3
4		-4
5		-5
6		-6
7		-7
8		-8
9		-9
10	1	-0
11	1	-1
12	1	-2
13	1	-3
14	1	-4
15	1	-5
16	1	-6
17	1	-7
18	1	-8
19	1	-9
20	2	-0
21	2	-1
22	2	-2
23	2	-3
24	2	-4
25	2	-5
26	2	-6
27	2	-7
28	2	-8
29	2	-9
30	3	-0
31	3	-1
32	3	-2
33	3	-3
34	3	-4
35	3	-5
36	3	-6
37	3	-7
38	3	-8
39	3	-9
40	4	-0
41	4	-1
42	4	-2
43	4	-3
44	4	-4
45	4	-5
46	4	-6
47	4	-7
48	4	-8
49	4	-9
50	5- 826654	-0



SEE DIAGRAM
826629 SHEET 3




OBSOLETE

1. VON DIESER ZEICHNUNG GIBT ES KEIN ORIGINAL
 OBSOLETE

TE Connectivity. All Rights Reserved.



DIMENSIONS:		DWN	MATERIAL		FINISH	
mm		CHK	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
0 PLC	±	PRODUCT SPEC	NAME AMPMODU II STIFTLAISTE 90DEG EINREIHIG			
1 PLC	±	—				
2 PLC	±	APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
3 PLC	±	—	A4		00779	C-826654
4 PLC	±	WEIGHT	—		RESTRICTED TO	
ANGLES	±	—	—		—	
		CUSTOMER DRAWING				SCALE
						SHEET
						1 of 1
						REV
						P2