

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	PART OBSOLESCENCE	01AUG2024	AR	VG


POS PER ROW	L +0.3 -0.5	PART-NO.
2	5.08	826942 -2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1- -0
11	27.94	1- -1
12	30.48	1- -2
13	33.02	1- -3
14	35.56	1- -4
15	38.10	1- -5
16	40.64	1- -6
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0
21	53.34	2- -1
22	55.88	2- -2
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7
28	71.12	2- -8
29	73.66	2- -9
30	76.20	3- -0
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- 826942 -0

SEE DIAGRAM
826629 SHEET 2

1 OBSOLETE

THERE IS NO ORIGINAL OF THIS DRAWING

TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN —	MATERIAL —	FINISH —		
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —	 TE Connectivity			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD —			NAME AMPMODU II STIFTLEISTE ZWEIREIHIG	
	PRODUCT SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO C-826942	RESTRICTED TO —
	APPLICATION SPEC —				
	WEIGHT —				
CUSTOMER DRAWING			SCALE —	SHEET 1 of 1	REV P1