


LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
NUMMER 828 697			2	CAD-NEUERSTELLUNG	31.08.89	—	WRULICH
VERWENDET FÜR			B1	ECR-06-016478	07-JUN-06	—	HESS
WAR NR.			B2	ECR-10-025774		KK	HMR

POLZ	L±0.4	BESTELL-NR.
—	—	—
2	5.08	<del>828 697-2</del> OBSOLETE
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1- -0
11	27.94	1- -1
12	30.48	1- -2
13	33.02	1- -3
14	35.56	1- -4
15	38.10	1- -5
16	40.64	1- -6
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0
21	53.34	2- -1
22	55.88	2- -2
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7
28	71.12	2- -8
29	73.66	2- -9
30	76.20	3- -0
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- 828 697 -0



1 MIN. 2.0µm ZINN ÜBER 1.27µm NICKEL (KONTAKTSPITZEN TEILWEISE BLANK)

CAD-ORIGINAL		
ZEICHNUNG NICHT ÄNDERN		
KONTAKTSTIFT	Cu Sn	1
STIFTGEHÄUSE	PBTP-gv	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

ZEICHNUNG GÜLTIG AB 35/89...

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - By -

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm	DWN	31.08.89	MATERIAL	FINISH
	WRULICH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	—	TE Connectivity	
	SCHAAR.			
±0.2 mm	APVD	—	NAME AMPMODU II STIFTLISTE EINREIHIG	
	—			
0 PLC ± -	PRODUCT SPEC	—	SIZE	CAGE CODE
	1 PLC ± -		A4	00779
2 PLC ± -	APPLICATION SPEC	—	DRAWING NO	RESTRICTED TO
	3 PLC ± -		C-828697	—
4 PLC ± -	WEIGHT	—		
	ANGLES ± -			
		CUSTOMER DRAWING	SCALE	SHEET
			4:1	1 OF 1
				REV B2