


LOC	DIST	1 REVISIONS		
—	—	P	LTR	2 DESCRIPTION
		A		LUG LENGTH CHANGE FROM 2mm to 1.75mm
				DATE 09JAN2013
				DWN KJK
				APVD RP

- ① 2.0µm min. Zinn über 1.27µm Nickel
- ② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ③ OBSOLETE

POLZ PRO REIHE	L±0.4	BESTELL-NR.
—	—	—
2	5.08	829 290 -2 ③
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1- — ③
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2- — ③
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2- — ③
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 829 290 -0



THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. RELEASED FOR PUBLICATION.

3	CONTACT	CuSn	①
2	CONTACT	CuSn	①
1	HOUSING	PBTP GV	GREEN
POS	DESCRIPTION	MATERIAL	SURFACE/COLOUR

DIMENSIONS: mm		DWN G.HOLAUS 17.07.89	MATERIAL SEE TABLE	FINISH SEE TABLE
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M.SCHAARSCHMIDT	TE Connectivity	
0 PLC ± -		APVD -		
1 PLC ± -		PRODUCT SPEC -	NAME AMPMODU II STIFTLEISTE 90	
2 PLC ± 0.2		APPLICATION SPEC -	SIZE A4	CAGE CODE 00779
3 PLC ± -		WEIGHT -	DRAWING NO C-829290	
4 PLC ± -			RESTRICTED TO -	
ANGLES ± -			SCALE 4:1	SHEET 1 OF 1
		CUSTOMER DRAWING	REV A	