



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	S0		AB	REV PER 0H14-0191-05	05-05	AA	DE

1. RECEPTACLE TO MATE WITH AMP LGH-1 LEAD ASSY.
2. MARKED PER MIL-STD-130.
- ~~3. MARKED PER MIL-STD-130 INCLUDING CUST P/N 15020-002.~~
4. PIN EYELET IS SOLDER DIPPED ON 1--7 ONLY.
5. SPECIAL TESTING/INSPECTION:
100% VISUAL WORKMANSHIP/APPEARANCE
100% DWV 30,000VDC @ S.L./AMBIENT CONDITIONS
6. .500 [12.70] DIA. AND REAR SURFACE SAND
BLASTED TO PROMOTE ADHESION TO POTTING MATERIAL.



5	TIN	.88 [22.4]	1.00 [25.4]	6-834333-8
-	TIN	.75 [19.0]	.88 [22.4]	5-834333-3
-	TIN	.88 [22.4]	1.00 [25.4]	5-834333-2
-	TIN	1.00 [25.4]	1.12 [28.4]	5-834333-1
-	TIN	1.12 [28.4]	1.25 [31.7]	5-834333-0
5	TIN-LEAD	.88 [22.4]	1.00 [25.4]	1-834333-8
4/6	TIN-LEAD	.88 [22.4]	1.00 [25.4]	1-834333-7
OBSOLETE	TIN-LEAD	.88 [22.4]	1.00 [25.4]	1-834333-6
OBSOLETE	GOLD	.75 [19.0]	.88 [22.4]	834333-7
OBSOLETE	GOLD	.88 [22.4]	1.00 [25.4]	834333-6
OBSOLETE	GOLD	1.00 [25.4]	1.12 [28.4]	834333-5
OBSOLETE	GOLD	1.12 [28.4]	1.25 [31.7]	834333-4
-	TIN-LEAD	.75 [19.0]	.88 [22.4]	834333-3
-	TIN-LEAD	.88 [22.4]	1.00 [25.4]	834333-2
-	TIN-LEAD	1.00 [25.4]	1.12 [28.4]	834333-1
-	TIN-LEAD	1.12 [28.4]	1.25 [31.7]	834333
REMARKS	PIN PLATING	DIM B	DIM A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	23-MAR-94	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
		CHK	11-APR-94								
DIMENSIONS: INCHES		C.SHELLY		NAME							
		C.SHELLY									
		APVD	11-APR-94	RECEPTACLE LGH-1 —							
		C.SHELLY									
		PRODUCT SPEC								—	
		APPLICATION SPEC								—	
MATERIAL		—		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
		—		A2	00779	C=834333		—			
EPOXY MLDG CMPD COLOR: BLACK		FINISH		WEIGHT		CUSTOMER DRAWING		SCALE	SHEET	1 of 1	REV
—		—		—		—		2:1	1	AB	AB