


IN AMERICAN PROJECTION

BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

THIS PRODUCT DESIGNED AND BUILT BY AMP INCORPORATED. NO LICENSE TO USE THAT DESIGN IN MANUFACTURE, OR TO USE ANY ISSUED OR PENDING PATENTS WHICH ARE INVOLVED, IS IMPLIED.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	A	REV. PER ECN 5375	12/1/69	[Signature]
	A	REV. PER ECN 5375	12/1/69	[Signature]
	C	ADDED - 4	1/1/70	[Signature]
	D	ADDED - 5	2/1/70	[Signature]
	E	ADDED - 6	3-11-77	[Signature]
	F	ADDED - 7	7-5-77	[Signature]
	G	ADDED - 8	7-5-77	[Signature]
	H	ADDED - 9	7-5-77	[Signature]
	J	REV. PER ECN. 8720	AG 3-20-79	[Signature]
	K	ADDED - 14	RM 7/1/80	[Signature]
	K	ADDED - 15	RM 7/1/80	[Signature]
	L	OBSOLETE 5, 14, 15 ECN 53070	2-4-87	[Signature]
	M	OBSOLETE -2, -6, -8, -9, -1-1, -1-2 ECN L1559	4-30-87	[Signature]
	N	OBS-3 ECN DF 0697	10-88	[Signature]
	P	REV. PER DF-474A	TS 5/81	[Signature]
	R	REV PER ECN DF-5972	JL 10/19/82	KJK

AMP P/N	"A"	
849486-1	12.00	
849486-2	5.00	OBSOLETE
849486-3	66.00	OBSOLETE
849486-4	28.00	
849486-5	14.25	OBSOLETE
849486-6	40.00	OBSOLETE
849486-7	24.50	
849486-8	16.00	OBSOLETE
849486-9	8.00	
1-849486-0	24.00	1-19-79
1-849486-1	144.00	AK OBS 7-19-79
1-849486-2	36.00	
1-849486-3	20.00	
1-849486-4	45.00	
1-849486-5	18.00	



△ TOLERANCE ON "A" DIMENSION : UP TO 24 = ± .12
24 & UP = ± 1%

△ MOLDED END TO MATE WITH LGH-I RECEPTACLE'S 833589, 834333-2, 830149-1, 846793-1, 846544-1, 858827-1 & ANY OTHER LGH-I RECEPTACLE WITH A BARREL DEPTH OF .88

3. COLOR OF LEAD WIRE WHITE UNLESS OTHERWISE SPECIFIED

1-849486-5	18.00±.12	13973-841416-0002 REV.	OBSOLETE
1-849486-4	45.00±.45		OBSOLETE
1-849486-3	20.00±.12		
1-849486-2	36.00±.36		OBSOLETE
1-849486-1	144.00±1.44		OBSOLETE
1-849486-0	24.00±.12	13973-841416-0001 REV.	
849486-9	8.00±.12		OBSOLETE
849486-8	16.00±.12		OBSOLETE
849486-7	24.50±.24		
849486-6	40.00±.40		OBSOLETE
849486-5	14.25±.12		OBSOLETE
849486-4	28.00±.28		
849486-3	66.00±.66		OBSOLETE
849486-2	5.00±.12		OBSOLETE
849486-1	12.00±.12		
PART NO.	A	CUSTOMER PART NUMBER	

QTY REQD	ITEM NO.	DWG SIZE	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION	SYMBOL
PARTS LIST					
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES .00 = ±.02 ANGLES = T .000 = ±.005			CONTRACT NO. DR <i>W. Kralj</i> 3-24-69		
MATERIAL: <i>H</i>			AMP INCORPORATED CAPTRON DIVISION ELIZABETHTOWN, PENNSYLVANIA		
FINISH: <i>H</i>			NAME LGH-I LEAD ASS'Y., MOLDED END ONE END, J1-21 CONTACT OTHER END		
			APPD <i>Ken R</i> 3-25-69		SIZE C
			DSGN APPD		CODE IDENT NO. 00779
			OTHER APPD		NUMBER 849486
			SCALE <i>---</i>		WT
					SHEET 1 OF 1

CUSTOMER DRAWING