





LOC		DIST		REVISIONS				
GP	00	REV	DATE	BY	CHK	APPV		
N2	REVISED PER ECO-13-019961	19DEC2013	RW	WH				
N1	REVISED PER ECO-09-020774	24AUG09	KK	AEG				



- △ POLYESTER, FLAME RETARDANT, COLOR: BLACK
- 2. HOUSING ACCEPTS P.C. BOARD, .055-.070 THICK
- △ PART NO. AND DATE CODE INK STAMPED, WHITE.
- △ CAVITY ENDS IDENTIFICATION (SEE TABLE)
- △ OBSOLETE PART NO.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ 2-86743-5	35 & P	4.600	4.200	3.800	3.600	3.754	3.634	70	△ 2-86743-6
△ 2-86743-3	25 & C	3.600	3.200	2.800	2.600	2.754	2.634	50	△ 2-86743-4
△ 2-86743-1	21 & Y	3.200	2.800	2.400	2.200	2.354	2.234	42	△ 2-86743-2
△ 1-86743-9	17 & U	2.800	2.400	2.000	1.800	1.954	1.834	34	△ 2-86743-0
△ 1-86743-7	22 & Z	3.300	2.900	2.500	2.300	2.454	2.334	44	△ 1-86743-8
△ 1-86743-5	20 & X	3.100	2.700	2.300	2.100	2.254	2.134	40	△ 1-86743-6
△ 1-86743-3	28 & F	3.900	3.500	3.100	2.900	3.054	2.934	56	△ 1-86743-4
△ 1-86743-1	29 & H	4.000	3.600	3.200	3.000	3.154	3.034	58	△ 1-86743-2
△ 86743-9	9 & K	2.000	1.600	1.200	1.000	1.154	1.034	18	△ 1-86743-0
△ 86743-7	33 & M	4.400	4.000	3.600	3.400	3.554	3.434	66	△ 86743-8
△ 86743-5	19 & W	3.000	2.600	2.200	2.000	2.154	2.034	38	△ 86743-6
△ 86743-3	15 & S	2.600	2.200	1.800	1.600	1.754	1.634	30	△ 86743-4
△ 86743-1	10 & L	2.100	1.700	1.300	1.100	1.254	1.134	20	△ 86743-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J. GALLUCCI 4-19-89		TE Connectivity HSG, CARD EDGE, DBL ROW, W/MTG EARS, .100	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING		NAME SIZE CASE CODE DRAWING NO A1 00779 C=86743	
MATERIAL		FINISH		RESTRICTED TO	
				SCALE 4:1 SHEET 1 OF 1 REV N2	