



- 1 MATERIAL: GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR: BLACK
- 2 PART NUMBER AND DATE CODE MARKED WHEN HOUSING SIZE PERMITS.
- 3 1.17±.38 CHARS. MARKED FIRST AND EVERY 5TH CAVITY, SAME SIDE OF PART NO. AND DATE CODE MARKING.
- 4 OBSOLETE PARTS; OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
7. NO PART NO. AND THE MARKING OF DATE CODE MAY BE ROTATED 90°.



OBSOLETE	ALL	6-87456-5	81.28	31	64	6-87456-6
	ALL	6-87456-3	73.66	28	58	6-87456-4
	ALL	6-87456-1	71.12	27	56	6-87456-2
	ALL	5-87456-9	60.96	23	48	6-87456-0
OBSOLETE	ALL	5-87456-7	83.82	32	66	5-87456-4
	ALL	5-87456-5	88.90	34	70	5-87456-6
OBSOLETE	ALL	5-87456-3	2.54	-	2	
	ALL	5-87456-1	76.20	29	60	5-87456-2
	NOTE #7	4-87456-9	5.08	1	4	5-87456-0
	ALL	4-87456-7	91.44	35	72	4-87456-8
	ALL	4-87456-5	68.58	26	54	4-87456-6
	ALL	4-87456-3	53.34	20	42	4-87456-4
	ALL	4-87456-1	66.04	25	52	4-87456-2
	ALL	3-87456-9	63.50	24	50	4-87456-0
	ALL	3-87456-7	55.88	21	44	3-87459-8
	ALL	3-87456-5	50.80	19	40	3-87456-6
OBSOLETE	ALL	3-87456-3	48.26	18	38	3-87456-4
	ALL	3-87456-1	45.72	17	36	3-87456-2
	ALL	2-87456-9	43.18	16	34	3-87456-0
	ALL	2-87456-7	40.64	15	32	2-87456-8
	ALL	2-87456-5	38.10	14	30	2-87456-6
	ALL	2-87456-3	35.56	13	28	2-87456-4
	ALL	2-87456-1	33.02	12	26	2-87456-2
	ALL	1-87456-9	30.48	11	24	2-87456-0
	ALL	1-87456-7	27.94	10	22	1-87456-8
	ALL	1-87456-5	25.40	9	20	1-87456-6
	ALL	1-87456-3	22.86	8	18	1-87456-4
	ALL	1-87456-1	20.32	7	16	1-87456-2
	ALL	87456-9	17.78	6	14	1-87456-0
	ALL	87456-7	15.24	5	12	87456-8
	NO PART #	87456-5	12.70	4	10	87456-6
	NO PART #	87456-3	10.16	3	8	87456-4
	NOTE# 7	87456-1	7.62	2	6	87456-2
	MARKING	UNMARKED HOUSING PART NUMBER	"L" DIM	NUMBER OF SPACES	NUMBER OF POSITIONS	MARKED HOUSING PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11-06-92		 TE Connectivity	
		CHK 11-30-92			
DIMENSIONS:		TO DIMENSIONS UNLESS OTHERWISE SPECIFIED:		NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 CENTERS SHORT ENTRY	
mm		APVD 11-30-92			
		PRODUCT SPEC			
		108-25020			
1 P/LC ±: - 1 P/LC ±: 0 2 P/LC ±0.5 3 P/LC ±0.13 4 P/LC ±: ANGLES ±0° 30'		APPLICATION SPEC		SIZE CASE CODE DRAWING NO RESTRICTED TO A 100779 C=87456 -	
MATERIAL		FINISH		WEIGHT	
		-		-	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV S5	