



1. CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54 TOLERANCE NON-CUMULATIVE
2. USE EXTRACTION TOOL 843996-3 TO REMOVE RECEPTACLE CONTACTS.
3. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D. RENAUD/D. SINISI
4. PART NO., AND DATE CODE IS MARKED IN AREA AS SHOWN WHEN HOUSING SIZE PERMITS (SEE TABLE).
5. 1,17±.38 CHARS. MARKED FIRST AND EVERY 5TH CAVITY, ONE SIDE.
6. MATERIAL: GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR: BLACK
7. NO PART NUMBER AND THE DATE CODE MARKING MAY BE ROTATED 90°




SECTION X-X



ISOMETRIC VIEW



SCALE 2:1



SCALE 2:1

	3	ALL	5-87483-3	93.98	81.28	31	64	5-87483-4
OBSELETE		ALL	5-87483-1	86.36	73.66	28	58	5-87483-2
OBSELETE		ALL	4-87483-9	83.82	71.12	27	56	5-87483-0
OBSELETE		ALL	4-87483-7	76.20	63.50	24	50	4-87483-8
		ALL	4-87483-5	73.66	60.96	23	48	4-87483-6
		ALL	4-87483-3	71.12	58.42	22	46	4-87483-1
		ALL	4-87483-1	66.04	53.34	20	42	4-87483-2
		ALL	3-87483-9	60.96	48.26	18	38	4-87483-0
		ALL	3-87483-7	58.42	45.72	17	36	3-87483-8
		ALL	3-87483-5	55.88	43.18	16	34	3-87483-6
		ALL	3-87483-3	50.80	38.10	14	30	3-87483-4
		ALL	3-87483-1	48.26	35.56	13	28	3-87483-2
		ALL	2-87483-9	43.18	30.48	11	24	3-87483-0
		ALL	2-87483-7	40.64	27.94	10	22	2-87483-8
		ALL	2-87483-5	35.56	22.86	8	18	2-87483-6
		ALL	2-87493-3	30.48	17.78	6	14	2-87483-4
		ALL	2-87483-1	27.94	15.24	5	12	2-87483-2
		NO PART #	1-87483-9	25.40	12.70	4	10	2-87483-0
		NO PART #	1-87483-7	22.86	10.16	3	8	1-87483-8
			1-87483-5	20.32	7.62	2	6	1-87483-6
		ALL	1-87483-3	78.74	66.04	25	52	1-87483-4
		ALL	1-87483-1	68.58	55.88	21	44	1-87483-2
		ALL	87483-9	63.50	50.80	19	40	1-87483-0
		ALL	87483-7	53.34	40.64	15	32	87483-8
		ALL	87483-5	45.72	33.02	12	26	87483-6
		ALL	87483-3	38.10	25.40	9	20	87483-4
		ALL	87483-1	33.02	20.32	7	16	87483-2
MARKING		UNMARKED HOUSING PART NUMBER	"L" DIM	"K" DIM	NUMBER OF SPACES	NUMBER OF POSITIONS	MARKED HOUSING PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SCHLAG BG 12-27-89		 TE Connectivity	
DIMENSIONS:		CHN P. SREMICH 10-5-93			
mm		APVD P. SREMICH 10-5-93		NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 CENTERS SHORT ENTRY	
		PRODUCT SPEC 108-25020			
		APPLICATION SPEC 114-25003, 114-25016			
		WEIGHT			
MATERIAL		FINISH		SIZE CASE CODE DRAWING NO RESTRICTED TO	
		-		A 100779 C=87483 -	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1 REV. W4	