





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECO-18-00976	13APR2018	RS	JO
	J1	PART OBSOLESCENCE	04FEB2025	KS	PS



- 1 CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54 [.100] TOLERANCE NON-CUMULATIVE.
- 2 USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 3 THIS HOUSING IS COMPATIBLE WITH MOD II WHROUDED HEADERS.
- 4 HOUSING WILL ACCOMODATE ALL MOD IV, IV.5 AND MOD V CONTACTS.
- 5 OBSOLETE PART NUMBER.
- 6 'AMP', PART NO. AND DATE CODE MARKED EITHER SIDE.
- 7 MARK SECOND AND EVERY FIFTH CAVITY, (ONE SIDE)
- 8 HOUSING: GLASS FILLED NYLON, BLACK
RELIEF: GLASS FILLED NYLON, BLACK
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN E.BRANDBERG 6-16-94		 TE Connectivity Ltd.				
			CHK P. SREMCICH 6-16-94						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME HOUSING ASSEMBLY, MOD IV, DBL ROW, 2.54[.100]				
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —						
	FINISH —		APPLICATION SPEC —						
MATERIAL 			WEIGHT	A2	CAGE CODE 00779	DRAWING NO C=87733		RESTRICTED TO —	
CUSTOMER DRAWING					SCALE 2:1	SHEET 1 of 2		REV J1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-
-	-	SEE SHEET 1	-	-	-


NONE	81.28 [3.200]	38.10 [1.500]	40.64 [1.600]	64	 5-87733-0
NONE	73.66 [2.900]	35.56 [1.400]	35.56 [1.400]	58	 4-87733-9
NONE	71.12 [2.800]	33.02 [1.300]	35.56 [1.400]	56	 4-87733-8
NONE	60.96 [2.400]	27.94 [1.100]	30.48 [1.200]	48	 4-87733-7
NONE	91.44 [3.600]	43.18 [1.700]	45.72 [1.800]	72	 4-87733-6
NONE	88.90 [3.500]	43.18 [1.700]	43.18 [1.700]	70	 4-87733-5
NONE	83.82 [3.300]	40.64 [1.600]	40.64 [1.600]	66	 4-87733-4
NONE	76.20 [3.000]	35.56 [1.400]	38.10 [1.500]	60	 4-87733-3
NONE	68.58 [2.700]	33.02 [1.300]	33.02 [1.300]	54	 4-87733-2
NONE	66.04 [2.600]	30.48 [1.200]	33.02 [1.300]	52	 4-87733-1
NONE	63.50 [2.500]	30.48 [1.200]	30.48 [1.200]	50	 4-87733-0
NONE	55.88 [2.200]	25.40 [1.000]	27.94 [1.100]	44	 3-87733-9
NONE	53.34 [2.100]	25.40 [1.000]	25.40 [1.000]	42	 3-87733-8
NONE	50.80 [2.000]	22.86 [.900]	25.40 [1.000]	40	 3-87733-7
NONE	48.26 [1.900]	22.86 [.900]	22.86 [.900]	38	 3-87733-6
NONE	45.72 [1.800]	20.32 [.800]	22.86 [.900]	36	 3-87733-5
NONE	43.18 [1.700]	20.32 [.800]	20.32 [.800]	34	 3-87733-4
NONE	40.64 [1.600]	17.78 [.700]	20.32 [.800]	32	 3-87733-3
NONE	38.10 [1.500]	17.78 [.700]	17.78 [.700]	30	 3-87733-2
NONE	35.56 [1.400]	15.24 [.600]	17.78 [.700]	28	 3-87733-1
NONE	33.02 [1.300]	15.24 [.600]	15.24 [.600]	26	 3-87733-0
NONE	30.48 [1.200]	12.70 [.500]	15.24 [.600]	24	 2-87733-9
NONE	27.94 [1.100]	12.70 [.500]	12.70 [.500]	22	 2-87733-8
NONE	25.4 [1.000]	10.16 [.400]	12.70 [.500]	20	 2-87733-7
ALL	81.28 [3.200]	38.10 [1.500]	40.64 [1.600]	64	 2-87733-6
MARKING	C	B	A	NO OF POSN	PART NUMBER

ALL	73.66 [2.900]	35.56 [1.400]	35.56 [1.400]	58	 2-87733-5
ALL	71.12 [2.800]	33.02 [1.300]	35.56 [1.400]	56	 2-87733-4
ALL	60.96 [2.400]	27.94 [1.100]	30.48 [1.200]	48	 2-87733-3
-	-	-	-	-	-
-	-	-	-	-	-
ALL	91.44 [3.600]	43.18 [1.700]	45.72 [1.800]	72	 2-87733-0
ALL	88.90 [3.500]	43.18 [1.700]	43.18 [1.700]	70	 1-87733-9
ALL	83.82 [3.300]	40.64 [1.600]	40.64 [1.600]	66	 1-87733-8
ALL	76.20 [3.000]	35.56 [1.400]	38.10 [1.500]	60	 1-87733-7
ALL	68.58 [2.700]	33.02 [1.300]	33.02 [1.300]	54	 1-87733-6
ALL	66.04 [2.600]	30.48 [1.200]	33.02 [1.300]	52	 1-87733-5
ALL	63.50 [2.500]	30.48 [1.200]	30.48 [1.200]	50	 1-87733-4
ALL	55.88 [2.200]	25.40 [1.000]	27.94 [1.100]	44	 1-87733-3
ALL	53.34 [2.100]	25.40 [1.000]	25.40 [1.000]	42	 1-87733-2
ALL	50.80 [2.000]	22.86 [.900]	25.40 [1.000]	40	 1-87733-1
ALL	48.26 [1.900]	22.86 [.900]	22.86 [.900]	38	 1-87733-0
ALL	45.72 [1.800]	20.32 [.800]	22.86 [.900]	36	 87733-9
ALL	43.18 [1.700]	20.32 [.800]	20.32 [.800]	34	 87733-8
ALL	40.64 [1.600]	17.78 [.700]	20.32 [.800]	32	87733-7 
ALL	38.10 [1.500]	17.78 [.700]	17.78 [.700]	30	 87733-6
ALL	35.56 [1.400]	15.24 [.600]	17.78 [.700]	28	 87733-5
ALL	33.02 [1.300]	15.24 [.600]	15.24 [.600]	26	 87733-4
ALL	30.48 [1.200]	12.70 [.500]	15.24 [.600]	24	 87733-3
ALL	27.94 [1.100]	12.70 [.500]	12.70 [.500]	22	 87733-2
ALL	25.4 [1.000]	10.16 [.400]	12.70 [.500]	20	 87733-1
MARKING	C	B	A	NO OF POSN	PART NUMBER

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL 

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13[.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN
E.BRANDBERG
6-16-94

CHK
P. SREMCIH
6-16-94

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity Ltd.

HOUSING ASSEMBLY, MOD IV,
DBL ROW, 2.54[.100]

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=87733

RESTRICTED TO
-

SCALE
2:1

SHEET
2 of 2

REV
J1

1471-9 (1/15)