




© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.  
 ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS  
 COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS				DATE	APPROVED
P	F	ZONE	LTR		
		K	ECO-15-004141	23APR15	RL



- ① THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS.
- ② WHEN PART IS PHYSICALLY TOO SMALL FOR THIS INFORMATION (SMALLER THAN 10 PDS.) MARK AS FOLLOWS:  
 2, 3, & 4 PDS. - "AMP" ONLY.  
 5 THRU 9 PDS. - MILITARY PART NO. ONLY.
- ③ MARKED .062±.015 HIGH CHARACTERS IN AREA SHOWN.
- 4. QUALITY CONFORMANCE INSPECTION PER MIL-C-55302 GROUP A, B, & C.
- 5. PACKAGED PER MIL-C-55302.
- ④ TOLERANCE NON-CUMULATIVE.
- ⑤ OBSOLETE
- 8. MARKED "CSA" LOGO ON PART.



MILITARY PART NO.	IB	IA	NO. OF PDS.	PART NUMBER	MILITARY PART NO.	IB	IA	NO. OF PDS.	PART NUMBER
M55302/127-361B	3.640	3.500	36	3-87968-5					
-351B	3.540	3.400	35	3-					
-341B	3.440	3.300	34	3-					
-331B	3.340	3.200	33	3-					
-321B	3.240	3.100	32	3-					
-311B	3.140	3.000	31	3-					
-301B	3.040	2.900	30	2-					
-291B	2.940	2.800	29	2-					
-281B	2.840	2.700	28	2-					
-271B	2.740	2.600	27	2-					
-261B	2.640	2.500	26	2-					
-251B	2.540	2.400	25	2-					
-241B	2.440	2.300	24	2-					
-231B	2.340	2.200	23	2-					
-221B	2.240	2.100	22	2-					
-211B	2.140	2.000	21	2-					
-201B	2.040	1.900	20	1-					
-191B	1.940	1.800	19	1-					
-181B	1.840	1.700	18	1-					
-171B	1.740	1.600	17	1-					
-161B	1.640	1.500	16	1-					
OBSOLETE	-151B	1.540	1.400	15	1-				
-141B	1.440	1.300	14	1-					
-131B	1.340	1.200	13	1-					
-121B	1.240	1.100	12	1-					
-111B	1.140	1.000	11	1-					
OBSOLETE	-101B	1.040	.900	10					
OBSOLETE	-091B	.940	.800	9					
-081B	.840	.700	8						
-071B	.740	.600	7						
-061B	.640	.500	6						
OBSOLETE	-051B	.540	.400	5					
OBSOLETE	-041B	.440	.300	4					
-031B	.340	.200	3						
M55302/127-371B	3.740	3.600	37	3-87968-6	M55302/127-021B	.240	.100	2	87968-1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±	CONTRACT NO DR J. Super 1/12/79	 Tyco Electronics Corporation Harrisburg, PA 17105-3608
	MATERIAL HSS. - DIALYL PHthalate, COLOR - BLUE CONTACTS - PHOS. BRONZE FINISH CONTACTS - .000050 GOLD OVER .000050 - .000100 NICKEL	
CHECKED: J.E. Seibert 1-18-79 APPD: A.R. Hoffman 1-19-79 APPD: CRK 2/11/81	DSGN APPD OTHER APPD	SIZE CODE IDENT NO DRAWING NO C 00779 87968
	SCALE #	SHEET 1 OF 1