





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED BY ECO-10-006013	31MAR2010	NCL	MBG
	C	REVISED PER ECN-25-307751	18MAR2025	WLS	RE



- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD / D.SINISI.
- 2 WIRE RANGE : >1,0 - 2,5 mm².
- 3 INSULATION RANGE : Ø2,7 - 4,0 mm.




SECTION A - A



SECTION B - B

	OBSOLETE	TIN PLATED	PHOSP.BRONZE	880623-4
	OBSOLETE		PHOSP.BRONZE	880623-3
		TIN PLATED	BRASS	880623-2
			BRASS	880623-1
	FINISH		MATERIAL	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NCLAPRESA 08DEC2014	TE Connectivity		
DIMENSIONS: mm		CHK FCHRISTIANO 08DEC2014			
		APVD LWPRADO 08DEC2014			
		PRODUCT SPEC			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	2 PLC ±0,3	RING TONG		
		3 PLC ±			
MATERIAL SEE TABLE	FINISH SEE TABLE	4 PLC ±			
		ANGLES ±1°			
-	-	WEIGHT	SIZE A3	CAGE CODE -	DRAWING NO C-880623
		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 OF 1	REV C