

4

3

2

1

© 2019 TE Connectivity. All Rights Reserved.

MATED WITH:



826629



167301-4



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA1	PARTS STATUS UPDATED	21JUL2022	SCB	PS

POS.	L±0.8	PART NUMBER
2	5.08	925366-2
3	7.62	925366-3
4	10.16	925366-4
5	12.70	925366-5
6	15.24	925366-6
7	17.78	925366-7
8	20.32	925366-8
9	22.86	925366-9
10	25.40	1-925366-0
11	27.94	1-925366-1
12	30.48	1-925366-2
13	33.02	1-925366-3
14	35.56	1-925366-4
15	38.10	1-925366-5
16	40.64	1-925366-6
17	43.18	1-925366-7
18	45.72	1-925366-8
19	48.26	1-925366-9
20	50.80	2-925366-0
21	53.34	2-925366-1
22	55.88	2-925366-2
23	58.42	2-925366-3
24	60.96	2-925366-4
25	63.50	2-925366-5
26	66.04	2-925366-6
27	68.58	2-925366-7
28	71.12	2-925366-8
29	73.66	2-925366-9
30	76.20	3-925366-0
31	78.74	3-925366-1
32	81.28	3-925366-2
33	83.82	3-925366-3
34	86.36	3-925366-4
35	88.90	3-925366-5
36	91.44	3-925366-6
37	93.98	3-925366-7
38	96.52	3-925366-8
39	99.06	3-925366-9
40	101.60	4-925366-0
41	104.14	4-925366-1
42	106.68	4-925366-2
43	109.22	4-925366-3
44	111.76	4-925366-4
45	114.30	4-925366-5
46	116.84	4-925366-6
47	119.38	4-925366-7
48	121.92	4-925366-8
49	124.46	4-925366-9
50	127.00	5-925366-0

OBSOLETE


1



PN 1-925366-0 FROM DIFFERENT CAVITIES AS SHOWN BELOW

VIEW A

SCALE 3:1



NOTES:

1

TE LOGO FOR 2 POSITON TO 19 POSITION PART NUMBERS
TE LOGO CAN BE ON EITHER SIDE (LEFT OR RIGHT) OF THE HOUSINGS, SEE VIEW A


2


TE LOGO FOR 20 POSITION TO 50 POSITION PART NUMBERS

3

PRODUCT SPECIFICATION - 108-25020 (MOD IV STANDARD CONTACT PRESSURE)
- 108-25021 (MOD IV INTERMEDIATE CONTACT PRESSURE)
- 108-25007 (MOD V HIGH CONTACT PRESSURE)

2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KARTHIK J K 23AUG2019	 TE Connectivity		
DIMENSIONS:		CHK HARI SURIYA 23AUG2019			
m/m	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD PRASHANTH S 23AUG2019	NAME AMPMODU IV RECEPTACLE HOUSING, SINGLE ROW WITHOUT STRAIN RELIEF		
	0 PLC ±0.2mm	3	SIZE A2		
	1 PLC ±		CAGE CODE 100779		
	2 PLC ±	APPLICATION SPEC 114-25003	DRAWING NO C-925366		
	3 PLC ±		RESTRICTED TO -		
	4 PLC ±	WEIGHT -	SCALE 5:1		
	ANGLES ±		SHEET 1 OF 1		
MATERIAL PA66 GREEN RAL 6001	FINISH -	CUSTOMER DRAW ING			REV AA1