





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED ECR-20-006447	22JUL2020	VI	SPB





3D VIEW
(SCALE 1/1)






(DRAWING 1.)
(SCALE 1/1)

ASSEMBLY VIEW(WITH BULB)
(SCALE 1/1)



SECTION C-C
(SCALE 1/1)



NOTE;



1. APPLIED BULB IS AS FOLLOWS: SEE DRAWING 1.
2. 0.15 MAX. WARPAGE AND 0.2 MAX. FLASH ARE PERMISSIBLE
3. SURFACE DEFECTS ARE NOT ACCEPTABLE AS FOLLOWS: SINK, WELD LINES, HAIRCRACKS, STAINS & SCORES
4. APPLIED PLUG ASSEMBLY P/N: 936184
5. SPC DIMENSION : ■

TOLERANCES UNLESS OTHERWISE SPECIFIED			
0 <XX<10	± 0.2		
10<XX<30	± 0.25		
30<XX	± 0.3		
ANGLES	± 3°		


control priority dimension; ■ CRITICAL, ☒ MAJOR, □ MINOR	
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL SEE TABLE	FINISH -

DWN	JM JEON
CHK	JW JUNG
APVD	HG CHO
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	0
CUSTOMER DRAWING	-


4	-	CuNiSi Alloy	EARTH TML	936813-101	1	1	1
3	-	CuNiSi Alloy	BULB SOCKET TML	936812-1	1	1	1
2	GRAY(RAL 7004)	SILICONE(LSR)	□ RING	936817-1	1	1	1
1	BROWN(RAL 8003)	PBT	CAP HSG	936264-4			1
1	GRAY(RAL 7036)	PBT	CAP HSG	936264-3		1	
1	BLACK(RAL 9011)	PBT	CAP HSG	936264-2		1	
1	IVORY(RAL 1015)	PBT	CAP HSG	936264-1	1		
NO.	COLOR	MATERIAL	DESCRIPTION	P/N	Q'TY		
TE Connectivity							
NAME							
BULB HOLDER 2P CAP ASS'Y FOR AMBER BULB —							
SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO		
A2	00779	C=936263			—		
SCALE			1:1	SHEET		1 of 1	REV
							C1



SECTION A-A
(SCALE 2/1)



SECTION B-B
(SCALE 2/1)



BULB POCKET LAYOUT
(SCALE 2/1)

ASSY P/N	Q'TY
936263-1	1
936263-2	1
936263-3	1
936263-4	1