






P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED(ECR-10-025267)	09,DEC'10	JH	HG
	B I	REVISED(ECR-16-005223)	12,APR'16	EW	KT
	C	REVISED(ECR-22-146627)	22,MAY'22	HC	KT
	C I	REVISED(ECR-25-235303)	18,FEB'25	JS	YH



LEAD FREE-NON SEALED CHIP RESISTOR CONNECTOR	1-936575-2	C
NON SEALED CHIP RESISTOR CONNECTOR FOR CAN	936575-1	C
ASSY DESCRIPTION	ASSY P/N	REV


CI	4	-	-	FRAME-CHIP RESISTOR FOR LEAD FREE	I	I
CI	3	WHITE	PBT-GF15	LEAD FREE CHIP RESISTOR CONNENTOR HSG	I	
	2	-	-	TAB WITH CHIP RESISTOR		
	1	WHITE	PBT-GF15	CHIP RESISTOR CONNECTOR HSG		I
	NO	COLOR	MATERIAL	DESCRIPTION	QT'Y	

NOTE

1. THE MATING PLUG ASSEMBLE P/N : 936582-1
2. 0.15 MAX. WARPAGE AND 0.2 MAX FLASH

3. CHIP CAPACITY : 121Ω +6% / -1%

 4 GENERAL TOLERANCE : ± 0.2 , $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	 TE Connectivity					
DIMENSIONS: mm		CHK -	NAME NON SEALED CHIP RESISTOR CONN'R					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ±- ±- ±- ±- ±- ±-	APVD -						
		PRODUCT SPEC -						
MATERIAL &MATERIAL -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT -	A3	00779	Ⓒ-936575	-		
finish_spec_2		CUSTOMER DRAWING			SCALE 5:1	SHEET 1	OF 2	REV C1

4

3

2

1

Ⓒ







Ⓒ

1-936575-2

LEAD FREE-NON SEALED CHIP RESISTOR CONNECTOR

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT



TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

C-

SCALE

SHEET

OF

REV

DIMENSIONS:

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

1 PLC

±

2 PLC

±

3 PLC

±

4 PLC

±

ANGLES

±

MATERIAL

FINISH