














LOC		DIST		REVISIONS					
P	LYR	REV	DESCRIPTION MODIFICATIONS			DATE	DWN DESS.	APVD APP.	
	A1		REVISED PER ECO-11-005150			28MAR2011	RK	HMR	
	A2		CORRECTED THE PN's IN NOTE IN ZONE A7 ON SHEET 1 OF 2			20JUL2016	KCD	SA	



Nota:
PARKAGING FOLLOWING SPEC TE CONNECTIVITY:107-18078 and 107-15368
PART TO USE WITH:
SOCKET HOUSING FOR POS. 1 TO 20 REF PN 953119-2 (BROWN) OR PN 1-953119-4 (WHITE)
SOCKET HOUSING FOR POS. 21 TO 40 REF PN 953119-1 (GREEN) OR PN 1-953119-3 (BLACK)
CONTACT MQS REF /144969-X; 1379418-X; 1379419-X
NUMBER MAXI OF WIRE PERMITTED:
40 WIRES SECTION 0.75mm2 (Ø maxi insult 1.9mm)
RECOMMANDATION SPEC:411-15597


THIS DRAWING IS A CONTROLLED DOCUMENT. CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AMP INCORPORATED. IL EST SOUSCRIPTIBLE D'UNE REVISION, CONNECTE LE SERVICE TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIERE REVISION.		DWN/DESSINE M. POLIFONT 08FEB2005	X. ROULLARD 09FEB2005		TE Connectivity	
DIMENSIONS: mm	TOLERANCES, UNLESS OTHERWISE SPECIFIED TOLERANCES, NON SPECIFIEES AUTREMENT PRECISEES: ±0.2	APVD/APPROUVE J. DAHER 09FEB2005	PRODUCT SPEC SPEC. PRODUCT 108-15178	APPLICATION SPEC SPEC. APPLICATION	NAME TITRE ASSEMBLY COVER 40 WAY MQS CABLE-LOCKING AT 15 DEG.	RESTRICTED TO RESERVE A
MATERIAL MATIERE PBT GF 20	FINISH FINITION -	WEIGHT MASSE APPROX 8.9gr	CAGE CODE 00779	DRAWING NO 953122	SIZE FORMAT A1	
CUSTOMER DRAWING		/PLAN CLIENT	UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 3:1	SHEET FEUILLE 1 OF 2	REV A2

LOC	DIST	REVISIONS					
		P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
F	00		-	SEE SHEET 1	-	-	-

953122-1	SHIELD	2	1	BLACK	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-2	SHIELD	2	1	GREY	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-3	SHIELD	2	1	WITHE	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-4	SHIELD	2	1	BLUE	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
TE CONNECTIVITY PART NUMBER	COMPONENT	Rep	Q.	COLOR	MATERIAL	CODING
953122-5	SHIELD	2	1	BLACK	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-6	SHIELD	2	1	GREY	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-7	SHIELD	2	1	WITHE	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
953122-8	SHIELD	2	1	BLUE	PBT GF 20	 ECHELLE 3:2
	LEVER	1	1	BLACK	PBT GF 20	
TE CONNECTIVITY PART NUMBER	COMPONENT	Rep	Q.	COLOR	MATERIAL	CODING

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AMP INCORPORATED.
IL EST INSÉPARABLE DE SES REVUES. CONSTATER LES REVUES.
TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIÈRE RÉVISION.

mm



MATERIAL
MATIERE

PBT GF 20

OTHER SPEC. SELECTED

0.2

±5°

FINISH

-

DWN/DRESSINE
M. POLIFONTE
CHK/VERIFIEE
X. ROUILLARD

APVD/APPROUVE
J. DAHER

PRODUCT SPEC
SPEC. PRODUIT
108-15178

APPLICATION SPEC
SPEC. APPLICATION

WEIGHT
MASSE APPROX 8.9gr

CUSTOMER DRAWING

08FEB2005
09FEB2005

09FEB2005

NAME
TITRE

ASSEMBLY COVER 40 WAY MOS
CABLE-LOCKING AT 15 DEG.

SIZE
FORMAT
A1

CAGE CODE
00779

DRAWING NO
No PLAN
C=953122

RESTRICTED TO
RESERVE A
-

DRYQUEMENT
POUR REFERENCE

SCALE
ECHELLE 3:1

SHEET
FEUILLE 2

OF
DE 2

REV
A2

TE Connectivity

TE