

THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG.
 BY AMP INCORPORATED. ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN.
 COPYRIGHT 19-



MATED WITH: PASSEND ZU:	LOC AI	DIST -	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG				DATE	DWN	APVD
-	-	-	P	LTR					
PROJEKT NR.: -				A2	EG00 0587 98	27-MAY-98	T.B.	-	
				A3	CHANGED REMARK FROM "SEE 116-18014" TO "SEE 1355049"	18-MAY-00	M.P.	V.H.	

Customer Drawing

for PN 964334

SEE 1355049

-	-	-	-	-	-	-	-
CUSTOMER PART NO	AMP PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	

DIMENSIONS: DIMENSIONEN: mm	DWN	27-MAY-98	MATERIAL	FINISH OBERFLAECHE/FARBE	-	
	CHK	18-MAY-00	AMP Deutschland GmbH D - 63225 Langen			
TOLERANCES UNLESS OTHERWISE SPECIFIED; ALLGEMEINTOLERANZEN	APVD	19-MAY-00				
	PRODUCT SPEC PRODUKTSPEZ.	-				
n. ISO 8015 p. ISO 2768 - mH -E r. DIN 16901 - 140	APPLICATION SPEC VERARBEITUNGSSPEZ.	-	NAME STANDARD-POWER-TIMER CONTACT TYP A STANDARD-POWER-TIMER KONTAKT TYP A			
	ANGLES/WINKEL	±	SIZE	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.	RESTRICTED TO NUR FUER
	WEIGHT GEWICHT	-	A4	00779	C- 964334	-
	CUSTOMER DRAWING /KUNDENZEICHNUNG		MASSTAB	BLATT	1 OF 1 VON 1	A3