

FOUR CONDUCTOR CABLE, MODIFIED POLYESTER INSULATED,
600 VOLT, 120°C, LIGHTWEIGHT

The complete requirements for procuring the wire described herein shall consist of this document and the issue in effect of Raychem Specification WCD 281.






Component wire -
99M0111



Part Number	Wire Size	Outside Diameter (mm)		Maximum Weight (kg/km)
		Nom	Max	
99M0141-28-*/**/*	28	1.75	1.93	6.18
99M0141-26-*/**/*	26	2.11	2.29	11.95
99M0141-24-*/**/*	24	2.35	2.53	14.21
99M0141-22-*/**/*	22	2.71	2.89	20.19
99M0141-20-*/**/*	20	3.37	3.62	31.15
99M0141-18-*/**/*	18	3.98	4.22	42.85
99M0141-16-*/**/*	16	4.58	4.82	67.98
99M0141-14-*/**/*	14	5.42	5.66	85.28
99M0141-12-*/**/*	12	6.27	6.51	111.65

COLOUR CODE: The '*' in the part number shall be replaced by a standard colour code designator in accordance with Mil Std 681.

eg: 99M0141-24-0/2/4/9, cores black, red, yellow, white.

DESIGN	PROD. MAN.	TECHNICAL	QA	MANUFACTURE
 28.5.97.	 5.6.97	 19/6/97.	 18/6/97	 19/6/97