


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03AUG2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS AND APPLICABLE PIPE SIZES

PART NUMBER	APPLICABLE STANDARD PIPE SIZE		AS SUPPLIED		AS RECOVERED			
			MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		NOMINAL INSTALLED WALL THICKNESS (W)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.
AP2000-6	4.76	0.187	6.00	0.236	4.70	0.185	1.00	0.039
AP2000-8	6.35	0.250	8.00	0.315	6.10	0.240	1.00	0.039
AP2000-10	8.00	0.315	10.00	0.394	7.40	0.291	1.00	0.039
AP2000-15	10.00	0.394	15.00	0.591	7.40	0.291	1.00	0.039

PRODUCT INFORMATION


- NON-FLAME RETARDANT
- MATERIAL: JACKET; IRRADIATED MODIFIED POLYOLEFIN : COLOUR BLACK
LINER; HOT-MELT ADHESIVE : COLOUR CLEAR
- SHRINK RATIO: 1.3:1
- LONGITUDINAL CHANGE 0 TO -10%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)

CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.


DIMENSIONS:
mm(Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN	03AUG2023
CHK	BASAVARAJA D A
APVD	03AUG2023
PRODUCT SPEC	SELVAPANDIAN B
APPLICATION SPEC	VLADIMIR NEMEC
PRODUCT SPEC	RW-1001
APPLICATION SPEC	114-120021
WEIGHT	-
CUSTOMER DRAWING	



NAME
AP-2000 TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	AP-2000	-
SCALE	NTS	SHEET	1 OF 1
REV	A		