


						IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE		IMPLIED TOLERANCES HOLE DIA AND LOCATIONS.±0.5mm DIMENSIONS UP TO 30mm...±1.5mm DIMENSIONS OVER 30mm...±5% UP TO A MAX OF.....±5mm ANGULAR DIMENSIONS.....±5°		TCPN EL6881-000 PART Alias UTX/DUL CCD38-50-SN-M12-DOUB Cat No CCD38-50-SN-M12-DOUB		TITLE CABLE CLEAT DUAL Ø38-50 M12 STRUT NUT TYPE DOUBLE											
LOC												DRAWN DG		DATE 17/3/2017		 TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia							
												CHECKED RN		APPROVED AT									
DIST	—	I	INITIAL RELEASE		17/3/2017	DG	AT	MATERIAL DESC															
	POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO		MATL SPEC/STD/DRG NO		PROCESS SPEC HEAT TREAT/PLATING NO		SIZE A3		PROJECTION 3RD ANGLE		SCALE NTS		DRAWING NO AU34803		SHEET OF REV 	