


THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

DRAWING NO
AU34995
THIS DRAWING IS A CONTROLLED DOCUMENT



STRUT NUT IS FOR REPRESENTATION PURPOSES ONLY

SIZE RANGE	INSERTS OPTION	LENGTH A ± 1 mm mm (inch)	DEPTH B ± 1 mm mm (inch)	BOLT HOLE CENTER C mm (inch)	MAX INSTALLED HEIGHT D ± 1 mm mm (inch)	MAX CABLE E mm (inch)	MAX CABLE F mm (inch)
CC15-26	CABLE CLEATS ONLY	87 (3.42)	55 (2.16)	56 (2.20)	53 (2.09)	$\varnothing 19$ (0.75)	$\varnothing 30$ (1.18)
	CLEATS WITH INSERTS					$\varnothing 15$ (0.59)	$\varnothing 26$ (1.02)
CC26-38	CABLE CLEATS ONLY	96 (3.78)	60 (2.36)	64 (2.52)	70 (2.76)	$\varnothing 27$ (1.06)	$\varnothing 42$ (1.65)
	CLEATS WITH INSERTS					$\varnothing 26$ (1.02)	$\varnothing 38$ (1.49)
CC38-50	CABLE CLEATS ONLY	114 (4.49)	60 (2.36)	80 (3.15)	85 (3.35)	$\varnothing 39$ (1.53)	$\varnothing 54$ (2.12)
	CLEATS WITH INSERTS					$\varnothing 38$ (1.49)	$\varnothing 50$ (1.96)
CC50-75	CABLE CLEATS ONLY	136 (5.35)	65 (2.56)	100 (3.93)	115 (4.53)	$\varnothing 51$ (2.00)	$\varnothing 79$ (3.11)
	CLEATS WITH INSERTS					$\varnothing 50$ (1.97)	$\varnothing 75$ (2.95)
CC75-100	CABLE CLEATS ONLY	164 (6.45)	70 (2.76)	126 (4.96)	150 (5.90)	$\varnothing 76$ (2.99)	$\varnothing 104$ (4.09)
	CLEATS WITH INSERTS					$\varnothing 75$ (2.95)	$\varnothing 100$ (3.93)
CC100-135	CABLE CLEATS ONLY	200 (7.87)	80 (3.15)	160 (6.30)	190 (7.48)	$\varnothing 101$ (3.97)	$\varnothing 139$ (5.47)
	CLEATS WITH INSERTS					$\varnothing 100$ (3.93)	$\varnothing 135$ (5.31)
CC135-175	CABLE CLEATS ONLY	266 (10.47)	91 (3.58)	217 (10.23)	237 (9.33)	$\varnothing 139$ (5.47)	$\varnothing 179$ (7.04)
	CLEATS WITH INSERTS					$\varnothing 135$ (5.31)	$\varnothing 175$ (6.88)
CC175-220	CABLE CLEATS ONLY	313 (12.32)	102 (4.01)	263 (10.35)	299 (11.77)	$\varnothing 179$ (7.04)	$\varnothing 224$ (8.82)
	CLEATS WITH INSERTS					$\varnothing 175$ (6.88)	$\varnothing 220$ (8.66)

SIZE RANGE CCXX-XX-XXX

MODIFICATION CODES	
-	CLEAT BODIES ONLY
INS	WITH EPDM INSERTS WITHOUT MOUNTING HARDWARE
FM	WITH EPDM INSERTS + FLAT MOUNT HARDWARE
SN	WITH EPDM INSERTS + STRUT NUT MOUNT HARDWARE
CM	WITH EPDM INSERTS + CENTER MOUNT HARDWARE


SUITABLE FOR ANY CENTER MOUNT APPLICATION.
CENTER MOUNTING HARDWARE NOT INCLUDED.




CCXX-XX CABLE CLEATS ONLY




CCXX-XX-INS CLEATS WITH INSERTS




CCXX-XX-SN STRUT NUT



CCXX-XX-FM FLAT MOUNT



CCXX-XX-CM CENTER MOUNT

LOC	—	B	ADDED ADDITIONAL XS AND XL SIZE	10/04/25	MI	CSM	IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE		IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm. ±1.5mm. DIMENSIONS OVER 30mm. ±5%. UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°.		TCPN REFER TABLE	TITLE CABLE CLEATS CUSTOMER DRAWING- SINGLE						
	—	A2	CC15-26 TABLE UPDATED	21/02/25	MI	CM					PART Alias UTX/DUL							
	—	A1	CC26-38-M10 DIMENSIONS ADDED AND 'D' DIMENSIONS UPDATED	25/08/22	JS	RN					Cat No REFER TABLE	DRAWN MI	DATE 18/03/25	 TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia				
DIST	—	A	CC15-26 DIMENSIONS ADDED	16/08/21	JS	RN	MATERIAL DESC -					CHECKED VA	APPROVED CSM					
	POS	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO AU34995	SHEET 1	OF 1	REV B		

8

7

6

5

4

3

2

1