

DRAWING NO FAD2530-2730-8-C


THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FAD2530-2730-8 SUITS CONDUCTOR

DEADEND

STRANDING/CONDUCTOR	COND. TYPE	DIAMETER	FITTING LAY
37/3.75	AAC/AAAC	26.25	RIGHT HAND
37/0.149	AAC/AAAC	26.49	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD2530-2730-8
DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
MATERIAL: ALUMINIUM ALLOY
NUMBER OF RODS: 8
ROD DIAMETER: 5.40mm
OVERAL LENGTH: 1655mm
END FINISH: BALLENDDED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: BLACK

PRODUCT LABEL

FAD2530-2730-8
 37/3.75 AAC/AAAC
 37/0.149 AAC/AAAC

WEIGHT: 1.75kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FAD2530-2730-8
ID:
DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
37/3.75 AAC/AAAC
37/0.149 AAC/AAAC
RANGE: 25.30 - 27.30
COLOUR-CODE: BLACK
QTY: 10 **WEIGHT:** **BATCH:**

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN -	PART Alias UTX/DUL FAD2530-2730-8	TITLE FULL-TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø25.30-Ø27.30 37/3.75 AAC/AAAC 37/0.149 AAC/AAAC							
DIST	—	I	NEW RELEASE	20-05-2013	RN	AT	MATERIAL DESC ALUMINIUM ALLOY	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FAD2530-2730-8-C	SHEET 1	OF 1	REV 1	
POS	REV	REVISION RECORD		DATE	DWN	APVD												