




CATALOGUE NUMBER: FCD0900-0925-5 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
7/3.00	COPPER	9.00	RIGHT HAND
7/0.118	COPPER	8.99	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FCD0900-0925-5
 DESCRIPTION: FULL-TENSION HARD DRAWN COPPER DEADEND
 MATERIAL: HARD DRAWN COPPER WIRE
 NUMBER OF RODS: 6
 ROD DIAMETER: 2.64mm
 OVERAL LENGTH: 720mm
 END FINISH: CHAMFERED
 FITTING LAY DIRECTION: RIGHT HAND
 COLOUR CODED: RED

BOX LABEL

P/N: FCD0900-0925-5
 ID:
 DESCRIPTION:
FULL-TENSION COPPER DEADEND
 7/3.00 COPPER
 7/0.118 COPPER
 RANGE: 9.00 - 9.25
 COLOUR-CODE: RED
 QTY: 30 WEIGHT: BATCH:

PRODUCT LABEL

FCD0900-0925-5
 7/3.00 COPPER
 7/0.118 COPPER

WEIGHT: 0.45kg
 BATCH NO:
 MONTH/YEAR:

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN - PART Alias UTX/DUL FCD0900-0925-5 Cat No FCD0900-0925-5	TITLE FULL-TENSION HARD DRAWN COPPER DEADEND (FCD) FITTING COND. RANGE: Ø 9.00 - Ø 9.25 7/3.00 COPPER 7/0.118 COPPER						
DIST	—	I	NEW RELEASE	16-05-2013	RN	AT	MATERIAL DESC HARD DRAWN COPPER WIRE			<table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">DRAWN RN</td> <td style="width: 50%;">DATE 16-05-2013</td> </tr> <tr> <td>CHECKED MN</td> <td>APPROVED AT</td> </tr> </table>	DRAWN RN	DATE 16-05-2013	CHECKED MN	APPROVED AT	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia	
DRAWN RN	DATE 16-05-2013															
CHECKED MN	APPROVED AT															
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FCD0900-0925-5-C	SHEET 1	OF 1	REV 1