




CATALOGUE NUMBER: FCD0990-1065-6 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
19/2.00	COPPER	10.00	RIGHT HAND
7/3.50	COPPER	10.50	RIGHT HAND
19/0.083	COPPER	10.54	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FCD0990-1065-6
DESCRIPTION: FULL-TENSION HARD DRAWN COPPER DEADEND
MATERIAL: HARD DRAWN COPPER WIRE
NUMBER OF RODS: 4
ROD DIAMETER: 3.65mm
OVERAL LENGTH: 790mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: PURPLE / YELLOW

PRODUCT LABEL

FCD0990-1065-6
 19/2.00 & 7/3.50 COPPER
 19/0.083 COPPER

WEIGHT: 0.64kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FCD0990-1065-6
ID:
DESCRIPTION:
FULL-TENSION COPPER DEADEND
19/2.00 & 7/3.50 COPPER
19/0.083 COPPER
RANGE: 9.90 - 10.65
COLOUR-CODE: PURPLE / YELLOW
QTY: 20 **WEIGHT:** **BATCH:**

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS. ±0.5mm. DIMENSIONS UP TO 30mm. ±1.5mm. DIMENSIONS OVER 30mm. ±5%. UP TO A MAX OF ±5mm. ANGULAR DIMENSIONS. ±5°.	TCPN - PART Alias UTX/DUL FCD0990-1065-6 Cat No FCD0990-1065-6	TITLE FULL-TENSION HARD DRAWN COPPER DEADEND (FCD) FITTING COND. RANGE: Ø9.90-Ø10.65 19/2.00 & 7/3.50 COPPER 19/0.083 COPPER	DRAWN RN CHECKED MN	DATE 13-05-2013 APPROVED AT	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia				
DIST	—	I	NEW RELEASE	13-05-2013	RN	AT	MATERIAL DESC HARD DRAWN COPPER WIRE			SIZE	PROJECTION	SCALE	DRAWING NO	SHEET	OF	REV	
POS	REV	REVISION RECORD			DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	A3	3RD ANGLE	NTS	FCD0990-1065-6-C	1	1	1