
CUSTOMER DRAWING



PART NAME		PRODU	"GA" = WIRE GAUGE			
	A	В	С	L	K	(AWG)
	min	min	min	max	min	
B-021-26-N	6.3	4.6	2.8	32	150	26
	(0.250)	(0.180)	(0.110)	(1.260)	(5.900)	

CABLE DIMENSIONS								
D	Е	F	(G±0.02)	(M±0.02)				
		min						
2.4 (0.095) TO	2.3 (0.090) TO	0.3	19	6				
6.3 (0.250)	4.6 (0.180)	(0.012)	(0.750)	(0.235)				

MATERIAL

- 1. & 6. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.
- 2. & 5. SOLDER PREFORMS WITH FLUX:

SOLDER: TYPE Sn63 per ANSI J-STD-006. FLUX: TYPE ROL0 per ANSI J-STD-004.


- 3., 4. & 7. MELTABLE RINGS: Thermally stabilized thermoplastic.
- 8. CONDUCTOR LEAD: AWG GA (see table). MIL-W-81822/13-GA-9. ETFE insulated silver plated solid conductor. Color: white
- 9. GROUND LEAD: MIL-W-81822/13-GA-G. ETFE insulated, silver-plated, solid conductor. Color: blue. GA= Gauge per table.

APPLICATION

A. The parts covered by this document are for use in terminating the primary conductor and the braided shield of a coaxial cable having tin or silver-plated conductor and shield, rated for at least 125° C and meeting the dimensional requirements listed.

B. Parts will meet the requirements of Raychem specification RT-1404 when installed per Raychem RPIP-500-03.

For best results, prepare the cable as shown:



=7	Έ	TE Conr	nectiv		/chem evices	TITLE: COAXIAL SOLDERSLEEVE DEVICE WITH PRE-INSTALLED LEAD SOLID WIRES			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE IN BETWEEN BRACKETS.					DOCUMENT NO: B-021-GA-N				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ROU	GLES: N/A JGHNESS IN PRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.			DOCUMENT REVISION: D		REVISION ISSUE DATE: 12-MAR-2020	
DRAWN BY: R. MAPALO		23-NOV-1998 CODE		CAGE CODE: 06090	ECO NUMBER: ECO-20-003669		SCALE: NONE	SIZE:	SHEET: 1 of 1

© 1998 - 2020 TE Connectivity Corporation. All Rights Reserved.