



Connector Body



M18 Conductor Clamping Bolt

PART/DRG NO.	QTY.	DESCRIPTION
01-403-0125	1	MV COPPER END TERM. BODY - 49.0 O/D 33.5 I/D O'HEAD TYPE CENTRE PALM WITH Ø13.0 HOLES & SLOT
01-701-0010	3	M18x1.5 19 A/F 41.0 LONG BRASS MULTI-SHEAR BOLT

Issued to: Commercial	Quality	Stores	Production	A	FIRST ISSUE			S.P.W	21.11.01
				Revision	Description			Name	Date
				Design/Drawn	S.P.WEST	Date	21 NOV 2001	Scale (UoS)	1:1.25
				Checked by	Approved by				
				Drawing/Part No.	02-403-0126			Revision.	A
				ASSEMBLY					

© THIS DRAWING IS COPYRIGHT AND IS ISSUED ON THE STRICT UNDERSTANDING THAT IT IS NOT REPRODUCED COPIED OR DISCLOSED TO A THIRD PARTY WITHOUT THE CONSENT IN WRITING OF TYCO ELECTRONICS

tyco
Electronics
Energy Division

B&H
Middlemore Lane West,
Redhouse Ind. Est. Aldridge,
West Midlands WS9 8EA
Phone: +44(0)1922 744144
Fax: +44(0)1922 744150

Material VARIES
Finish VARIES
Tolerances (UoS) ±0.3
Remove all Burrs and Sharp Edges
All Threads to BS3643 Pt 2

IF IN DOUBT ASK! - DO NOT SCALE

Part Description
MV COPPER END TERMINATION - 49.0 O/D 33.5 I/D
OVERHEAD TYPE CENTRE PALM WITH Ø13.0 HOLES
& SLOT

Part Description
MV COPPER END TERM. BODY - 49.0 O/D 33.5 I/D
O'HEAD TYPE CENTRE PALM WITH Ø13.0 HOLES & SLOT