



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	24JAN2024	YB	AK

LABEL AND LINER DESIGN



PRESENTATION



QTY PER BAG: 500

TE PN: 4-1768016-7

All dimensions in mm [INCHES]

Kiss cut

- Kiss cut
- Back slit
- Perforation
- 2 kiss cut enductions
- Die cut
- Adhesive cut
- 45° die cut

Grid removed: NO
Sales unit: The label

PRINTING		
Color	Color	Color
1 WHITE	5	
2	6	
3	7	
4	8	

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [inches]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL SEE TABLE	FINISH

DWN	24JAN2024
Y. BONINO	
CHK	24JAN2024
Y. BONINO	
APVD	25JAN2024
A. KEAN	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	-

MATERIAL		CLEAR POLYVINYLCHLORID (PVC)	
ADHESIVE TYPE		PERMANENT ACRYLIC	
LINER		GLASSINE PAPER	
		TE Connectivity	
NAME		Part Description	
		BKM-15046-9	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	A00YM	C=4-1768016-7	-
SCALE	NTS	SHEET	1 OF 1
REV	B		

4-1768016-7