


| REVISIONS | | | | | |
|-----------|-----|-----------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| A | | INITIAL RELEASE | 03SEP2021 | MN | AK |

BKM-7546-9 SHOWN AS LAYOUT EXAMPLE



All dimensions in mm [INCHES]

| DESCRIPTION | PART NUMBER | LABELS PER SHEET | LABELS ACROSS | MIN CABLE DIAMETER | | MAX CABLE DIAMETER | | LABEL WIDTH (A) | | LABEL HEIGHT (B) | | PRINTABLE AREA HEIGHT (C) | | NET WEIGHT (g) |
|-------------|-------------|------------------|---------------|--------------------|-------|--------------------|-------|-----------------|-------|------------------|-------|---------------------------|-------|----------------|
| | | | | mm | Inch | mm | Inch | mm | Inch | mm | Inch | mm | Inch | |
| BKM-3823-9 | 5-1768016-4 | 40 | 10 | 3.2 | 0.125 | 8.9 | 0.351 | 23 | 0.905 | 38 | 1.496 | 10 | 0.394 | 0.26 |
| BKM-7523-9 | 5-1768016-7 | 20 | 10 | 8 | 0.313 | 15.9 | 0.627 | 23 | 0.905 | 75 | 2.953 | 25 | 0.984 | 0.52 |
| BKM-7546-9 | 6-1768016-2 | 10 | 5 | 8 | 0.313 | 15.9 | 0.627 | 46 | 1.811 | 75 | 2.953 | 25 | 0.984 | 1.20 |
| BKM-15023-9 | 4-1768016-4 | 10 | 10 | 8 | 0.313 | 39.8 | 1.567 | 23 | 0.905 | 150 | 5.906 | 25 | 0.984 | 1.03 |
| BKM-15046-9 | 4-1768016-7 | 5 | 5 | 8 | 0.313 | 39.8 | 1.567 | 46 | 1.811 | 150 | 5.906 | 25 | 0.984 | 1.84 |
| BKM-23025-9 | 5-1768016-1 | 6 | 6 | 8 | 0.313 | 65.3 | 2.57 | 25 | 0.984 | 230 | 9.055 | 25 | 0.984 | 1.52 |
| BKM-23050-9 | 5-1768016-2 | 3 | 3 | 8 | 0.313 | 65.3 | 2.57 | 50 | 1.969 | 230 | 9.055 | 25 | 0.984 | 3.03 |

| TOLERANCES mm [INCHES] | |
|------------------------|-------------|
| LABEL HEIGHT: | ±0.3 [012] |
| LABEL WIDTH: | ±0.3 [012] |
| WEB WIDTH: | ±0.8 [031] |
| VERTICAL REPEAT: | ±0.8 [031]* |
| HORIZONTAL REPEAT: | ±0.8 [031]* |
| PRINT POSITIONING: | ±0.8 [031]* |
| LEFT MARGIN: | ±0.4 [016] |
| QUANTITY: | -0 % +2 % |
| *NON ACCUMULATING | |

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|--|-----|--------------------------------|----------------------------|-----|---|---|---|-----|---|---|---|-----|---|---|---|-----|---|---|---|-----|---|---|--------|--|---|---|
| MATERIAL | | CLEAR POLYVINYL CHLORIDE (PVC) | | | | | | | | | | | | | | | | | | | | | | | | |
| ADHESIVE TYPE | | PERMANENT ACRYLIC | | | | | | | | | | | | | | | | | | | | | | | | |
| LINER | | GLASSINE PAPER | | | | | | | | | | | | | | | | | | | | | | | | |
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN M. NUTTALL 03SEP2021 | | | | | | | | | | | | | | | | | | | | | | | | |
| DIMENSIONS: mm [INCHES] | | CHK M. NUTTALL 03SEP2021 | | | | | | | | | | | | | | | | | | | | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED | | APVD A. KEAN 03SEP2021 | | | | | | | | | | | | | | | | | | | | | | | | |
| <table border="1"> <tr><td>0</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>1</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>2</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>3</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td>4</td><td>PLC</td><td>±</td><td>-</td></tr> <tr><td colspan="2">ANGLES</td><td>±</td><td>-</td></tr> </table> | | 0 | | PLC | ± | - | 1 | PLC | ± | - | 2 | PLC | ± | - | 3 | PLC | ± | - | 4 | PLC | ± | - | ANGLES | | ± | - |
| 0 | PLC | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | PLC | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | PLC | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | PLC | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | PLC | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| ANGLES | | ± | - | | | | | | | | | | | | | | | | | | | | | | | |
| MATERIAL SEE TABLE | | PRODUCT SPEC TTDS-056 | SIZE A2 | | | | | | | | | | | | | | | | | | | | | | | |
| FINISH - | | APPLICATION SPEC - | CAGE CODE C2290 | | | | | | | | | | | | | | | | | | | | | | | |
| | | WEIGHT SEE TABLE | DRAWING NO BKM_CD_TABLE | | | | | | | | | | | | | | | | | | | | | | | |
| | | CUSTOMER DRAWING | RESTRICTED TO - | | | | | | | | | | | | | | | | | | | | | | | |
| | | SCALE NTS | SHEET 1 of 1 | | | | | | | | | | | | | | | | | | | | | | | |
| | | REV A | | | | | | | | | | | | | | | | | | | | | | | | |