

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	RELEASED	17APR2020	RK	HL

BSTS/BSTS-FR SCD




Table 1: Dimensions mm(*inches*)

Size	As Supplied		Recovered			
	Inside Diameter Minimum (D)		Inside Diameter Maximum (d)		Wall Thickness (W)	
	mm	<i>in.</i>	mm	<i>in.</i>	mm	<i>in.</i>
-03	7.62	(0.300)	2.54	(0.100)	1.78	(0.070)
-04	10.16	(0.400)	3.81	(0.150)	1.78	(0.070)
-07	19.05	(0.750)	5.59	(0.220)	2.54	(0.100)
-11	27.94	(1.100)	9.53	(0.375)	3.05	(0.120)
-13	33.02	(1.300)	9.65	(0.380)	3.05	(0.120)
-15	38.10	(1.500)	12.70	(0.500)	3.56	(0.140)
-17	43.18	(1.700)	12.70	(0.500)	3.56	(0.140)
-20	50.80	(2.000)	19.05	(0.750)	4.06	(0.160)
-27	68.58	(2.700)	22.86	(0.900)	4.06	(0.160)
-30	76.20	(3.000)	31.75	(1.250)	4.06	(0.160)
-35	88.90	(3.500)	31.75	(1.250)	4.06	(0.160)
-40	101.60	(4.000)	44.45	(1.750)	4.06	(0.160)
-45	114.30	(4.500)	44.45	(1.750)	4.06	(0.160)

Color: Standard Black
 Non-Standard White, Yellow, Red and Clear (Clear is non-flame retardant)

Reference Specification: 108-120034 BSTS/BSTS-FR Specification

TE Connectivity. All Rights Reserved.



DIMENSIONS: MILLIMETERS (INCHES)	DWN J. Bitter 11NOV2018	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T. Licko -	TE Connectivity	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD T. Licko -		
	PRODUCT SPEC 108-120034	NAME BSTS/BSTS-FR SCD	
	APPLICATION SPEC -	SIZE A4	CAGE CODE 06090
	WEIGHT -	DRAWING NO G-BSTS/BSTS-FR	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 of 1
		REV D	