


REVISIONS					
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	0	CREATION	22JUIL98	JB	AD
	A	MIS A JOUR BRAS ET CLAVETTES	04JAN98	JB	AD
	B	EQ00-0172-99	21APR99	JB	AD
	C	ECR-16-007414	23MAY2016	JD	AG



ECHELLE 3:10

BRAS (Acier galvanise)
 ARM (galvanized steel)

BOULON M12 (revetement anti-corrosion)
 M12 BOLT (anti-corrosion coated)

ECROU ET RONDELLE
 (acier protege anti-corrosion)
 NUT AND WASHER
 (anti-corrosion coated steel)

VIS TRCC M10 (acier protege anti-corrosion)
 TRCC M10 SCREW (anti-corrosion coated steel)

CLAVETTE (plastique)
 WEDGE (plastic)

EMBOUT FUSIBLE OPTIONNEL (all alu)
 OPTIONAL SHEARD HEAD (alloy alu)

PN	DESIGNATION DESCRIPTION	CAPACITES (mm2) CAPACITIES
1273956-1	PA295	2 x 50 TO 95
1273956-2	PA235	2 x 25 TO 35

TOLERANCES UNLESS OTHERWISE SPECIFIED: -
 TOLERANCES NON SPECIFIEES: -

FINISH FINITION -

DIMENSIONS:

mm

DWN /DESSINE 22JUIL98
 J. BERLAND

MATERIAL MATIERE -

CHK /VERIFIE -
 M. BAIJOT

APVD /APPROUVE -
 G PORCHERAY

PRODUCT SPEC SPEC. PRODUIT -

APPLICATION SPEC SPEC. APPLICATION -

WEIGHT MASSE APPROX. 922g

NAME TITRE PA 295 - PA 235

SIZE FORMAT A4

CAGE CODE 00779

DRAWING NO No PLAN

C=1273956

RESTRICTED TO RESERVE A -

CUSTOMER DRAWING /PLAN CLIENT

UNIQUEMENT POUR REFERENCE

SCALE ECHELLE 1:5

SHEET FEUILLE

OF DE

REV C

RELEASED FOR PUBLICATION
 LIBRE A LA DIFFUSION
 ALL RIGHTS RESERVED.
 TOUS DROITS RESERVES.
 THIS DRAWING IS UNPUBLISHED.
 DIFFUSION RESTREINTE
 COPYRIGHT copyr ight _d8Ye -

TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES):
 0 PLC /DEC: ±0
 1 PLC /DEC: ±0.1
 2 PLC /DEC: ±0.2
 3 PLC /DEC: ±0.3
 4 PLC /DEC: ±0.4
 ANGLES ±

