


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	CREATION	17JUN2015	JB	AG



REFERENCE	PN	Codets ERDF ERDF Codets	CAPACITE PRINCIPAL Capacities main mm <sup>2</sup>	CAPACITES DERIVES Capacities tap mm <sup>2</sup>	COUPLE DE RUPTURE Breaking shear head torque
P2T70-150	2832082-1	67-31-483 67-31-485	35-150	PMCC	11Nm

2011

RELEASED FOR PUBLICATION  
LIBRE A LA DIFFUSION

ALL RIGHTS RESERVED  
TOUS DROITS RESERVES.

THIS DRAWING IS UNPUBLISHED.  
DIFFUSION RESTREINTE

BY -  
© COPYRIGHT 2011

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
TOLERANCES NON SPECIFIEES: -

DIMENSIONS: mm	DWN/DESSINE BERLAND	17JUN2015	MATERIAL MATIERE	-	FINISH FINITION	-		
	CHK/VERIFIE NEDELLEC	-	<b>TE</b> TE Connectivity					
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIVANT DE DECIMALES): 0 PLC/DEC: ±0 1 PLC/DEC: ±0 2 PLC/DEC: ±0 3 PLC/DEC: ±0 4 PLC/DEC: ±0 ANGLES ±	APVD/APPROUVE GUICHARD	-						
	PRODUCT SPEC SPEC. PRODUIT	-	NAME TITRE	P2T70-150				
	APPLICATION SPEC SPEC. APPLICATION	-	SIZE FORMAT	A4	CAGE CODE	-		
	WEIGHT MASSE APPROX.	-	DRAWING NO No PLAN	C-2832082				
	CUSTOMER DRAWING /PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE	1:2	SHEET FEUILLE	OF DE	REV A