





POS-NO.	DESCRIPTION	QUANTITY					
1	Main insulation part (PBT)	2					
2	2 Half frame ring connector (Al-alloy)						
3	Bolt with socket head M8x50 (steel, SW6)	2					
4	Washer (M10, steel)	2					
5	5 Side wedges (PBT)						
6	Steel hexagon nut DIN 934, M10	2					
7	Adapter part (Brass, tin-plated)	4					
8	Protection cap for the tap clamp (PP plastic)	4					
9	Teeth element (Brass, tin-plated)						
10	10 Grub screw for the tap conductor (Brass, tin-plated SW 11 Frame for the bow-type tap clamp(Al-alloy)						
11							

	BURR PROJECTION:			CTION:		DEBUR AND BREAK SHARP	DO NOT SCALE DRAWING	REV	revision:	
			FORM BOUN	D MEASUR	JRE: EDGES			confidential and proprietary to Tyco Electronics Corporation and it		
						DIMENSION:	subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronic personnel, without written authorization from Tyco Electronics Corporation, Harrisburg Pennsylvania USA.			
			NOT FORM B	OUND ME	ASURE:	mm				a
	NAME	SIGNA	TURE D	ATE			DESCRIPTION: HEL-6877; PN: 664194-000			
DRAWN	S. Pollakowski		02.09	9.2021	RING CONNECTOR					
CHK'D							with pyrami			
APPV'D							Main: 4X95-120SM / 4X120-150SE			
						Branch: 35-120SM, 50-150SE, 10-95RM, 16-120RE				
Tyco Electronics Raychem GmbH a TE Connectivity Ltd. company Trachenbergring 85 12249 Berlin (Germany)					DWG NO.	6877	7	A3		
			WEIGHT:	0,9kg	SCALE: 1:1	SHEET:	1 OF 1			