


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	Customer Drawing of CGPE-HW-12-A1-0-15MM	17SEP2019	RS	DV



		As Supplied				As Recovered	
		L	Expanded Jacket Wall (W)	Expanded I.D. (D)	Maximum Tilt of Cutting Section (A)	Maximum Recovered I.D. (d)	Recovered Jacket Wall (W1)
TE P/N	TE Description	MM	MM	MM	MM	MM	MM
2949076003	CGPE-HW-12-A1-0-15MM	15±1	1.25±0.25	12.7±0.75	1	7.5	2.0±0.1

MATERIAL: CGPE-HW-12 is fabricated from irradiated Modified flexible Polyolefin
COLOUR: Black

NOTE:
Refer to specification of 108-120008 for detailed product properties

DIMENSIONS:		DWN	17SEP2019	MATERIAL	-		FINISH	-							
mm		RS		<div>TE Connectivity</div>											
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	17SEP2019							RZ					
		APVD	17SEP2019							DV					
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		NAME											
		108-120008													
		APPLICATION SPEC		CGPE-HW-12-A1-0-15MM											
		-													
		SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO								
		WEIGHT	-	A4	-	C- CGPE-HW-12-A1-0-15MM									
CUSTOMER DRAWING				SCALE		NTS		SHEET		1 OF 1		REV		A	
