

CGPE - 105
Flexible, Commercial Grade, Polyolefin,
Heat-Shrinkable Tubing




Table 1: Dimensions mm(*inches*)

Size	As Supplied		Recovered							
	Inside Diameter Minimum (D)		Inside Diameter Maximum (d)		Wall Thickness (W)					
	mm	<i>in.</i>	mm	<i>in.</i>	Minimum		Maximum		Nominal	
	mm	<i>in.</i>	mm	<i>in.</i>	mm	<i>in.</i>	mm	<i>in.</i>	mm	<i>in.</i>
3/64	1.17	.046	0.58	.023	0.33	.013	0.48	.019	0.40	.016
1/16	1.60	.063	0.79	.031	0.35	.014	0.50	.020	0.43	.017
3/32	2.36	.093	1.17	.046	0.43	.017	0.58	.023	0.50	.020
1/8	3.17	.125	1.57	.062	0.43	.017	0.58	.023	0.50	.020
3/16	4.74	.187	2.36	.093	0.43	.017	0.58	.023	0.50	.020
1/4	6.35	.250	3.17	.125	0.56	.022	0.71	.028	0.64	.025
3/8	9.50	.375	4.74	.187	0.56	.022	0.71	.028	0.64	.025
1/2	12.70	.500	6.35	.250	0.56	.022	0.71	.028	0.64	.025
3/4	19.05	.750	9.50	.375	0.69	.027	0.84	.033	0.76	.030
1	25.40	1.000	12.70	.500	0.76	.030	1.01	.040	0.88	.035
1-1/2	38.10	1.500	19.05	.750	0.86	.034	1.17	.046	1.01	.040
2	50.80	2.000	25.40	1.000	0.96	.038	1.32	.052	1.14	.045



For More Details See CGPE - 105 Specification, TEC - 108 - 120008

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2017 CGPE-105

DIMENSIONS: mm	DWN	07-JUNE-17			TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA		
	CHK	J. Bitter					
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-	NAME		CGPE - 105		
	PRODUCT SPEC	TEC-108-120008	APPLICATION SPEC		Flexible, Commercial Grade, Polyolefin, Heat - Shrinkable Tubing		
0 PLC ± -	WEIGHT	0	SIZE	A4	CAGE CODE	06090	
1 PLC ± -	CUSTOMER DRAWING		DRAWING NO	CGPE-105		RESTRICTED TO	-
2 PLC ± -			SCALE	None	SHEET	1 OF 1	REV
3 PLC ± -							
4 PLC ± -							
ANGLES ± -							