


1.0 PERFORMANCE

- 1.1 THIS COUPLER MEETS THE FUNCTIONAL PERFORMANCE AS DEFINED IN RAYCHEM SPECIFICATION D-6021.
- 1.2 OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
- 1.3 ALTITUDE: SEA LEVEL TO 50,000 FEET.
- 1.4 SALT SPRAY CORROSION RESISTANCE: 500 HOURS.
- 2.0 CONNECTORS AND CONTACTS
- 2.1 CONNECTORS, CONTACTS AND INTERMATEABILITY AS DEFINED IN TABLE 1, BELOW.

TABLE 1, CONNECTORS								
PORTS	CONNECTOR CONTACT		MATING CONNECTOR					
BUS	D-621-0434	D-602-0126 (PIN)	DK-621-0433-1S					
STUB	D-621-0440	D-602-0126 (PIN)	DK-621-0439-4S					

FOUR STUB COUPLER SCHEMATIC



			SPECIFICATION CONTROL DRAWING				
DRAWN	DATE		SIZE	CODE IDENT. NO.	DWG. NO.		REV
T RATZLAFF JAN222003		tyco /Electronics	A	06090	D-500	0-0255-431	NC
cad file T31552B.DWG					T	0.1557 0.05 0	
			DO	NOT SCALE	THIS DRAWING	SHEET 2 OF 2	