





1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. MODULE IS SUPPLIED WITHOUT CONTACTS.
(CAVITIES TO SUIT 6 OFF MC5 CONTACTS)

							MATERIAL		© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH UK. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH UK. GENERAL TOLERANCES UNLESS OTHERWISE STATED: ±0.4mm ON WHOLE NUMBERS ±0.2mm ON ONE PLACE DECIMALS ±0.1mm ON TWO PLACE DECIMALS ±1/2° ON ANGLES ±0.05mm ON DRILLED HOLES ALL DIAMETERS TO H7 REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED. DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED.		 DEUTSCH ST LEONARDS ON SEA, EAST SUSSEX, TN38 9RF TEL. +44 (0)1424 852721		TITLE PIN INSERT MODULE DMC-M CONNECTOR ENVELOPE DETAIL		DRAWING NUMBER 458235-ENV	
							HEAT TREATMENT & FINISH									
							PACKAGING									
A	57090	ADH	RBC	JAK	NJT	27/04/09										
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE	APP. I.E.D.		SCALE	2:1						