




DRAWING NUMBER

603596-ENV

A3


BS 8888
THIRD ANGLE
PROJECTION
IF IN DOUBT, ASK



SIZE	PART NUMBER	A MAX	B MAX	ØC MAX	ØD MAX
08	AS808	20.19	4.26	12.00	17.66
10	AS810	20.19	4.26	15.00	20.76
12	AS812	20.19	4.26	19.05	25.16
14	AS814	20.19	4.26	22.22	28.36
16	AS816	20.19	4.26	25.40	31.46
18	AS818	20.19	4.26	28.57	34.76
20	AS820	20.19	5.02	31.75	38.16
22	AS822	20.19	5.02	34.92	41.26
24	AS824	20.19	5.02	38.10	44.56

NOTES:-

1. PART NUMBER BREAKDOWN AND DATE CODE EXAMPLE:-



A	55176	ADH	NDL	JAK	IKG	04/12/07
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE

MATERIAL	ALUMINIUM ALLOY
HEAT TREATMENT & FINISH	BLACK CAD ON ZINC
PACKAGING	
APP. I.E.D.	-

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH UK. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH UK.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.
±0.4mm ON WHOLE NUMBERS
±0.2mm ON ONE PLACE DECIMALS
±0.1mm ON TWO PLACE DECIMALS
±1/2° ON ANGLES
±0.05mm ON DRILLED HOLES
ALL DIAMETERS TO 0.10
REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.
DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED

TITLE
PROTECTIVE CAP
PLUG ASSY TYPE 8
ENVELOPE DRAWING



DRAWING NUMBER
603596-ENV