





SHELL SIZE	ØA MAX	B MAX	C MAX	THREAD D
8	17.63	31.45	15.0	7/16 -28 UNEF 2A
10	20.73	31.45	15.0	9/16 -24 UNEF 2A
12	25.13	31.45	15.0	11/16 -24 UNEF 2A
14	28.33	31.45	15.0	13/16 -20 UNEF 2A

NOTES;-

1. BATCH No. & PART No. BREAKDOWN.

DEUTSCH ASDD6 ** - **P/S *-975P RP654321

SERIES _____
SHELL STYLE _____
ARRANGEMENT _____

BATCH NUMBER EXAMPLE
MODIFICATION CODE
KEYWAY ORIENTATION
P=PIN OR S=SOCKET


MATERIAL

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.

GENERAL TOLERANCES UNLESS OTHERWISE STATED.

±0.4mm ON WHOLE NUMBERS
±0.2mm ON ONE PLACE DECIMALS
±0.1mm ON TWO PLACE DECIMALS
±1/2° ON ANGLES
±0.05mm ON DRILLED HOLES

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.

DEUTSCH
LTD

EAST GRINSTEAD, WEST SUSSEX, RH19 1RW TEL:- (01342) 410033

TITLE ASDD PLUG
MOD CODE 975P
ENVELOPE DETAILS

DRAWING NUMBER

610745-ENV

HEAT TREATMENT & FINISH

03.07.07

IKG

SCALE

N.T.S.

DIMS. IN MILLIMETRES

APP. BUS. UNIT

CHECKED

DRAWN

54412

ISSUE

CHANGE NOTE

APP. ENG.