



NOTES

1. DIMENSIONS ARE FOR REFERENCE ONLY.


2. PART NUMBER & BATCH NUMBER EXAMPLE :-





3. CONNECTOR PROVIDED WITH 16mm² CRIMP CONTACT.



PANEL CUT-OUT



VIEW SHOWING PROTRUSION OF CRIMP CONTACT WHEN INSTALLED



ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE
B	55804	NDL	JAK	JAK	IKG	01/05/08
A	55563	NDL	JAK	JAK	DRW	04/03/08

MATERIAL	----
HEAT TREATMENT & FINISH	----
PACKAGING	----
APP. I.E.D.	----

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH UK. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH UK.

GENERAL TOLERANCES UNLESS OTHERWISE STATED:
 ±0.4mm ON WHOLE NUMBERS
 ±0.2mm ON ONE PLACE DECIMALS
 ±0.1mm ON TWO PLACE DECIMALS
 ±1/2° ON ANGLES
 ±0.05mm ON DRILLED HOLES
 ALL DIAMETERS ϕ 0.10

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.

DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED

SCALE 2:1

TITLE
 2 HOLE RECEPTACLE
 ASHD2. MOD 975Y.
 ENVELOPE DETAILS



DRAWING NUMBER
 610820-ENV