



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02JUL2021	TC	MT



(a) AS SUPPLIED



(b) RECOVERED

SIZE INCHES	H MIN (a)	H MAX (b)	W (b)
3/32	2.4	1.2	0.51 ± 0.08
1/8	3.2	1.6	0.51 ± 0.10
3/16	4.8	2.4	0.51 ± 0.10
1/4	6.4	3.2	0.64 ± 0.10
3/8	9.5	4.8	0.64 ± 0.10
1/2	12.7	6.4	0.64 ± 0.10
3/4	19.0	9.5	0.76 ± 0.12
1	25.4	12.7	0.89 ± 0.16
1-1/4	31.5	15.0	1.10 ± 0.10
1-1/2	38.0	19.0	1.02 ± 0.18

© 20 BY - a TE Connectivity Ltd. company. All Rights Reserved.

Printed on 14 Jul 2021 11:19 (GMT Standard Time) from TE357681

DIMENSIONS: mm	DWN T. CORREIA	02JUL2021	MATERIAL	-	FINISH	-
	CHK N. PRZYBYLSKA	02JUL2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. TAYLOR	02JUL2021				
	0 PLC ±-	PRODUCT SPEC	NAME	DR-25-TW TUBING		
1 PLC ±0.1	RK-6008/2	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ±0.01		-	A 4	06090	©-DR-25-TW	-
3 PLC ±0.001	WEIGHT	-	CUSTOMER DRAWING			
4 PLC ±0.0001			SCALE	DNS	SHEET	1 OF 1
ANGLES ±-					REV	A

