




REV
NC

DRB16-60S*E-L018

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P17208	4-5-01	RDR



7. MATING TORQUE REQUIREMENT: 30-35 IN-LB [3.38-3.95NM].

6. WIRE ROUTER CAP IS INCLUDED WITH PLUG (-L018 MOD).

5. THIS PLUG MATES WITH DRB12-60P*(N)E-**** RECEPTACLE (* = A,B,C,D KEYS; **** = ALL MODIFICATIONS). CONSULT FACTORY FOR MODS.

4. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

3. ITEMS SOLD SEPARATELY: SECONDARY LOCK: WB-60S*
INTERFACE FLANGE: DRBF-2*

2. DIMENSION TOLERANCE: $\pm .025$ [.64].

1. DIMENSIONS ARE IN INCHES [mm].

NOTES:

8. SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

7. MATERIAL: PLUG: PLASTIC
SEAL/GROMMET: RUBBER
BOLT/CLIP: STEEL

CONTACT SIZE	MIN. INSUL. O.D. [mm]	MAX. INSUL. O.D. [mm]	WIRE RANGE [mm ²] REF ONLY
16	.053 [1.346]	.120 [3.048]	14-20 AWG [2.0-0.5]
20	.040 [1.016]	.095 [2.413]	16-20 AWG [1.0-0.5]

SIGNATURE & DATE	
DR	S. PALLUTH 03/30/01
CHK	W. W. 4-4-01
PE	R. P. 4/2/01
APPD	D. Meyer 4/3/01
SCALE	NONE


PLUG, 60 CONTACTS
KEYS A,B,C & D
"E" SEAL, -L018 MOD
COLOR: BLACK
DRB SERIES

ENVELOPE


CP	EP059	MATL. CODE
The Deutsch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545		
DRB16-60S*E-L018		
DWG SIZE	CODE 11139	SHEET 1 OF 2

REV	DRB16-60S*E-L018
NC	


REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
	SEE SHEET 1	4-5-01	RDR




DRB16-60SAE-L018
KEY ARRANGEMENT -A-



DRB16-60SBE-L018
KEY ARRANGEMENT -B-



DRB16-60SCE-L018
KEY ARRANGEMENT -C-



DRB16-60SDE-L018
KEY ARRANGEMENT -D-

NOTES:

SIGNATURE & DATE	
DR	S. PALLUTH 03/30/01
CHK	R. M. 4-4-01
PE	L. P. 4/2/01
APPD	D. Meyer 4/10/01
SCALE	NONE

PLUG, 60 CONTACTS
KEYS A,B,C & D
"E" SEAL, -L018 MOD
COLOR: BLACK
DRB SERIES
ENVELOPE

CP	EP059	MATL CODE
The Deutsch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545		
B	DRB16-60S*E-L018	
DWG SIZE	CODE 11139	SHEET 2 OF 2