



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER PCN-E-16-016968	11JAN2017	MGM	DM





- 8 PART MODIFICATION: PIN CONTACT TAILS.
- 7 FLANGE SEAL IS CUSTOMER SUPPLIED.
- 6 SURFACE FINISH: 32 RMS OR BETTER; \square .005 [.12]
- 5. THIS RECEPTACLE MATES WITH DRC16-40S-XXXX. (XXXX = ALL MODIFICATIONS)
- 4. CONTACT PLATING - TIN.
- 3. MATERIAL - HOUSING: PLASTIC; SEAL: RUBBER; INSERT: STEEL.
- 2. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOWN).
- 1. DIMENSION TOLERANCE: \pm .025 [.64]; CUTOUT: \pm .010 [.25].

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN
DRC10-40P-A004	DRC10-40P-A004

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. PALLUTH 05MAR2001			
DIMENSIONS: IN [mm]		CHK V. TOMSA 18SEP2003			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 22SEP2003		NAME RECEPTACLE, FLANGED	
0 PLC \pm		PRODUCT SPEC		40 #16 SIZE CONTACTS	
1 PLC \pm		APPLICATION SPEC		COLOR: BLACK -A004 MOD	
2 PLC \pm		WEIGHT 112.1(g)		SIZE A3	CAGE CODE 4AFU8
3 PLC \pm		CUSTOMER DRAWING		DRAWING NO. DRC10-40P-A004	RESTRICTED TO -
4 PLC \pm		SCALE 1:1		SHEET 1 OF 2	REV G
ANGLES \pm					
FINISH					

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



RECOMMENDED CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. PALLUTH 05MAR2001	TE Connectivity	
DIMENSIONS: IN [mm]		CHK V. TOMSA 18SEP2003		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 22SEP2003	NAME RECEPTACLE, FLANGED 40 #16 SIZE CONTACTS COLOR: BLACK -A004 MOD	
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- MATERIAL		PRODUCT SPEC -	SIZE A3	
FINISH -		APPLICATION SPEC -	CAGE CODE 4AFU8	RESTRICTED TO -
		WEIGHT 112.1(g)	DRAWING NO DRC10-40P-A004	
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2
			REV G	