




DRC13-70PA-B027  
CODING A


SCALE 2:1



CODING  
Kodierung

DRC13-70PB-B027  
CODING B


SCALE 2:1



CODING  
Kodierung

DRC13-70PC-B027  
CODING C


SCALE 2:1



CODING  
Kodierung

DRC13-70PD-B027  
CODING D

SCALE 2:1



CODING  
Kodierung

REVISIONS		DATE	OWN	APVD
P.	LTN	DESCRIPTION		
-		SEE SHEET 1	-	-

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140 CENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY. Fremdstoleranzen nach DIN 16901-140. Es gilt die Ausgabe 1982-11.		DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMESSUNGEN UND TOLERANZEN GEMÄSS GPS (ISO STANDARDS).	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)		DWN: VIJETH N BHARADWAJ CHK: A. RACLAWSKI 07MAY2022	
DIMENSIONS: MASSENHEITEN: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS ACC. TO ISO 8015 DIN 16901-140	APVD: A. WOEBER 07MAY2022	NAME: 70POS.PIN CE SIZE 16.HEADER ASSY 70pol.Stiftkontakt Groesse 16.Gehauese Assy
MATERIAL: SEE TABLE Siehe Tabelle	FINISH/SCHICHEL/FARBE: SEE TABLE Siehe Tabelle	WEIGHT: 171.68g GEWICHT	RESTRICTED TO: NUR FÜR: -
CUSTOMER DRAWING		SIZE: A   00779	SCALE: 1:1



SIZE: A   00779	DRAWING NO: DRC13-70PX-B027	SHEET: 2	OF: 2	REV: B3
-----------------	-----------------------------	----------	-------	---------