



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER PCN-21-118564	07MAR2022	DRK	IG



KEY ORIENTATION

TCPN	ALIAS PART NUMBER
DRC26-50S01	DRC26-50S01
DRC26-50S02	DRC26-50S02
DRC26-50S03	DRC26-50S03
DRC26-50S04	DRC26-50S04
DRC26-50S05	DRC26-50S05
DRC26-50S06	DRC26-50S06
DRC26-50S07	DRC26-50S07
DRC26-50S08	DRC26-50S08
DRC26-50S09	DRC26-50S09
DRC26-50S10	DRC26-50S10

5 MATERIAL: HOUSING: PA46 30% GF (BLACK); BOLT: STEEL, TRIVALENT ZINC PLATED (ROHS COMPLIANT); CLIP: STEEL; GROMMET: VMO

4. THIS PLUG MATES WITH 09D41107L01 THRU 10-**** AND DRC20-50P01 THRU 10 -**** RECEPTACLE. (**** = ALL MODIFICATIONS)

3. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

2. RECOMMENDED RETAINING BOLT TORQUE: 25-28 IN-LB [2.82-3.16NM]

1. PLUG IS SUPPLIED WITH DUST CAP. (NOT SHOWN)

NOTES:

CONTACT SIZE	MIN. O.D.	MAX. O.D.	WIRE GAUGE RANGE REF ONLY
20	.040 [1.016]	.095 [2.413]	16 - 20 [1.00 - .50mm ²]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V TOMSA 11OCT1994	STE TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK D MEYER 20JUL2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R REED 20JUL2000	NAME PLUG 50 CONTACTS, SIZE 20 DRC SERIES	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [.64] 4 PLC ±		PRODUCT SPEC 108-151052	SIZE A2	
MATERIAL 5		FINISH -	APPLICATION SPEC -	CAGE CODE 00779
		WEIGHT -	DRAWING NO G-DRC26-50SXX	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 3:2	SHEET 1 OF 1
			REV B	