




3D VIEW



REV		REVISIONS		
REV	SYM	DESCRIPTION	DATE	APPROVED
B		DT04-08PA-P021		
	NC	NEW RELEASE PER E.O. P16727	6/13/00	R.D.R.
	A	REVISED PER E.O. P20196	5/7/09	R.D.R.
	B	REVISED PER E.O. P20274	9-1-09	RDR

- NOTES:
- DIMENSIONS ARE IN INCHES [MILLIMETERS].
 - DIMENSIONS ARE $\pm .025$ [0.63] UNLESS OTHERWISE SPECIFIED.
 - THIS DT04-08PA-P021 MATES WITH DT06-08SA-**** (**** = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.
 - ORIENTATION OF "DEUTSCH" AND "-P021" TO BE OPTIONAL.
 - THE 8 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 52 AMPS.

SIGNATURE & DATE		DT 8 WAY RECEPTACLE KEY ARRANGEMENT A 8 PIN BUSBAR-NICKEL PLATED COLOR; GREY	EP	MATL. CODE
DR	R. MCCORD 4/23/09		3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK			DEUTSCH INDUSTRIAL	
PE	R. Messinger 7/28/09		B DT04-08PA-P021	
APPD		ENVELOPE	DWG SIZE	CODE 11139 SHEET 1 OF 1
SCALE	2:1	WT		