





| P | LTR | DESCRIPTION                      | DATE      | DWN | APVD |
|---|-----|----------------------------------|-----------|-----|------|
|   | NC  | NEW RELEASE PER E.O. PI5936      | 26FEB1999 | -   | RDR  |
|   | A   | REVISED AND REDRAWN PER E.O. 166 | -         | -   | RDR  |
|   | C   | REVISED PER PCN-24-226269        | 06JAN2025 | AJT | MB   |
|   |     |                                  |           |     |      |



3D VIEW



4. MATERIAL:
- CONNECTOR: PA66 GF15, GRAY
  - CAP:PA66 GF15, BLACK
  - WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)
  - PINS:COPPER ALLOY, NICKEL PLATED

3. THE 12 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 78 AMPS, 13 AMPS PER PIN.
2. FOR WIRE, CONTACT PERFORMANCE, AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.
1. MATES WITH DT06-12SA-XXXX (XXXX = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

|                                        |  |                                |              |                                                                                                       |                    |                                |
|----------------------------------------|--|--------------------------------|--------------|-------------------------------------------------------------------------------------------------------|--------------------|--------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>P. BURKE                | 08MAY2000    |  TE Connectivity |                    |                                |
|                                        |  | CHK<br>-                       | 15MAY2000    |                                                                                                       |                    |                                |
| DIMENSIONS:<br>INCHES[mm]              |  | APVD<br>R. REED                | 16MAY2000    | NAME<br>DT 12 WAY RECEPTACLE KEY ARRANGEMENT<br>12 PIN BUSBAR-NICKEL PLATED<br>COLOR:GREY             |                    |                                |
|                                        |  | PRODUCT SPEC<br>108-151009     |              |                                                                                                       |                    |                                |
|                                        |  | APPLICATION SPEC<br>114-151009 |              | SIZE<br>A3                                                                                            | CAGE CODE<br>00779 | DRAWING NO<br>G-DT04-12PA-P021 |
| MATERIAL<br>4                          |  | WEIGHT<br>18 g                 |              | RESTRICTED TO<br>-                                                                                    |                    |                                |
|                                        |  | CUSTOMER DRAWING               | SCALE<br>2:1 | SHEET<br>1                                                                                            | OF<br>1            | REV<br>C                       |