


printed on 22 Jan 2025 12:46 (Eastern Standard Time) from TE354946



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER PCN E-21-003453	04MAY2022	AP	IG
	A3	REVISED PER PCN 22-148090	27JUL2022	GB	IG
	B	REVISED PER PCN-23-192205	06FEB2024	RK	CB
	E	REVISED PER PCN-25-232976	22JAN2025	AJ	CB

TE INTERNAL PN	DEUTSCH PN
DT04-12PA-LE01	DT04-12PA-LE01
DT04-12PB-LE01	DT04-12PB-LE01
DT04-12PC-LE01	DT04-12PC-LE01
DT04-12PD-LE01	DT04-12PD-LE01

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF ONLY
16	.088 [2.24]	.145 [3.68]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. YOHANNES 18SEP2002	TE Connectivity		
DIMENSIONS: in [mm]		CHK R. MESSENGER 03MAY2005			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BEARD 27APR2005			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0° 30' 0"		PRODUCT SPEC 108-151009			
MATERIAL		APPLICATION SPEC 114-151009	NAME 12 WAY RECEPTACLE DT SERIES		
FINISH		WEIGHT 80.88g	SIZE A3	CAGE CODE 4AFU8	DRAWING NO DT04-12PX-LE01
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 2	RESTRICTED TO REV E

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2017

© COPYRIGHT 2002


BY TE CONNECTIVITY

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


DT04-12PA-LE01
KEY ARR. -A-
HOUSING COLOR : GRAY
((FLANGE AND WELD CAP ARE BLACK FOR ALL KEY ARR.))




DT04-12PB-LE01
KEY ARR. -B-
HOUSING COLOR : BLACK




DT04-12PC-LE01
KEY ARR. -C-
HOUSING COLOR : GREEN



DT04-12PD-LE01
KEY ARR. -D-
HOUSING COLOR : BROWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. YOHANNES 18SEP2002		 TE Connectivity									
		CHK R. MESSENGER 03MAY2005											
DIMENSIONS: in [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 12 WAY RECEPTACLE DT SERIES									
		0 PLC ±		PRODUCT SPEC 108-151009		SIZE A3		CAGE CODE 4AFU8		DRAWING NO G-DT04-12PX-LE01		RESTRICTED TO -	
		1 PLC ±											
		2 PLC ±											
		3 PLC ± .025 [0.64]		APPLICATION SPEC 114-151009		WEIGHT 80.88g		SCALE 1:1		SHEET 2 OF 2		REV E	
		4 PLC ±											
MATERIAL 		FINISH ANGLES ±0° 30' 0"		CUSTOMER DRAWING									